

## Displayport to DVI Cable, Displayport with Latches to DVI-D Single Link Adapter (M/M), 6 ft.

MODEL NUMBER: **P581-006**



### Description

The P581-006 DisplayPort to DVI-D Cable Adapter (M/M) allows you to connect a computer with a DisplayPort connection to a high-definition television or monitor with a DVI input. Digital video signals are passed through with full 1080p video resolution. Fully molded ends are designed to last a long time.

The six-foot P581-006 is a passive adapter that requires the host computer to have a DP++ dual-mode connector, which allows HDMI and DVI signals to be passed through. Check your computer's documentation for compatibility.

### Features

- DisplayPort Male to DVI-D Male, 6 ft.
- Single-link adapter with latches
- Molded ends
- 1080p resolution
- Passive adapter requires the connected computer have DP++ (DisplayPort ++) dual-mode port

## Specifications

| OVERVIEW           |              |
|--------------------|--------------|
| UPC Code           | 037332148032 |
| INPUT              |              |
| Cable Length (ft.) | 6            |

### Highlights

- DisplayPort Male to DVI-D Male, 6 ft.
- Single-link adapter with latches
- Molded ends
- 1080p resolution
- Passive adapter requires the connected computer have DP++ (DisplayPort ++) dual-mode port

### System Requirements

- Not for use with MST Hubs. For compatibility with MST Hubs, use a DisplayPort 1.2 compliant product such as P581-006-V2

### Package Includes

- DisplayPort to DVI-D Cable Adapter, Single-Link Adapter with Latches (M/M), 6 ft.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                      |                          |
|--------------------------------------|--------------------------|
| Cable Length (m)                     | 1.8                      |
| <b>PHYSICAL</b>                      |                          |
| Color                                | Black                    |
| Shipping Dimensions (hwd / cm)       | 22.86 x 17.78 x 1.27     |
| Shipping Dimensions (hwd / in.)      | 9.00 x 7.00 x 0.50       |
| Shipping Weight (kg)                 | 0.17                     |
| Shipping Weight (lbs.)               | 0.37                     |
| <b>CONNECTIONS</b>                   |                          |
| Side A - Connector 1                 | DISPLAYPORT (MALE)       |
| Side B - Connector 1                 | DVI-D SINGLE LINK (MALE) |
| Connector Plating                    | Nickel                   |
| Contact Plating                      | Gold                     |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                          |
| Technology                           | DVI; DisplayPort         |
| <b>WARRANTY</b>                      |                          |
| Product Warranty Period (Worldwide)  | 3-year limited warranty  |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>