

DisplayPort 1.2 to HDMI Active Adapter Cable, Gripping HDMI Plug, HDCP 2.2, 4K @ 60 Hz (M/M), 12 ft.

MODEL NUMBER: P582-012-HD-V2A



HDCP 2.2-compliant cable connects the DisplayPort™ output on your PC or Mac to a 4K-enabled HDMI monitor, projector or television.

Description

The P582-012-HD-V2A DisplayPort 1.2a to HDMI Active Adapter Cable (M/M) connects a DisplayPort-enabled PC or Mac to the HDMI port on a 4K monitor, projector or television. With a DisplayPort male connector on one end and a gold-plated high-grip HDMI male connector on the other, this cable requires no separate power adapter. It lets you continue using an existing 4K HDMI display without the extra expense of buying a new DisplayPort monitor.

Recommended for displaying crystal-clear video on a large monitor or digital sign, this cable supports full UHD video resolutions up to 4K at 60 Hz (3840 x 2160) as specified in HDMI 2.0. The P582-012-HD-V2A also supports rich, full audio (if your DisplayPort card supports audio passthrough) and the latest HDCP 2.2 standards.

Because it's an active adapter, the 12-foot P582-012-HD-V2A is compatible with Single-Mode and Dual-Mode (DP++) DisplayPort output. It's perfect for use with graphics cards, such as AMD Eyefinity, that don't output DP++ signals.

The corrosion-resistant gold-plated HDMI connector and contacts provide maximum conductivity and minimize data loss. Its special high-grip plug prevents a loose or accidentally disconnected cable from causing picture loss. Integral strain relief with ridges on each end gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

Features

Send UHD DisplayPort 1.2a Signals to a 4K HDMI Display Connects DisplayPort PC or Mac to a 4K-enabled HDMI monitor, projector or HDTV. Recommended for displaying video on a large monitor or digital sign. DisplayPort and high-grip HDMI male connectors. No separate power adapter required.

Vibrant Video Quality Supports UHD video resolutions up to 4K @ 60 Hz (3840 x 2160), as specified in HDMI 2.0. Supports HDCP 2.2, audio and EDID. Active adapter compatible with Single-Mode and Dual-Mode (DP++) DisplayPort output. Recommended for graphics cards, such as AMD Eyefinity, that don't output DP++ signals.

Superior Materials for Superior Performance Gold-plated HDMI connector and contacts for maximum conductivity and minimum data loss. Special high-grip HDMI plug prevents accidental disconnections. Integral strain relief provides cable and connectors with flexibility and reduces stress.

Highlights

- Supports video resolutions up to 4K @ 60 Hz (3840 x 2160), as specified in HDMI 2.0
- Compliant with latest HDCP 2.2 standards and EDID
- No separate power adapter required
- High-grip HDMI plug prevents accidental disconnections

Package Includes

- P582-012-HD-V2A DisplayPort 1.2a to HDMI Active Adapter Cable (M/M), 12 ft.



Specifications

OVERVIEW	
UPC Code	037332200754
Technology	HDMI; DisplayPort
INPUT	
Cable Length (ft.)	12
Cable Length (m)	3.7
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	1.27 x 25.40 x 30.48
Shipping Dimensions (hwd / in.)	0.50 x 10.00 x 12.00
Shipping Weight (kg)	0.27
Shipping Weight (lbs.)	0.60
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>