

VGA/PS2/Audio Combo Cable Kit for KVM Switch B006-VUA4-K-R, 10 ft. (3.05 m)

MODEL NUMBER: P757-010



Highlights

- Connects a PS/2 Computer to B006-VUA4-K-R KVM Switch
- All-in-1 construction and slim size makes management and organization of cables much easier
- KVM Switch side of the cable kit consists of a HD15 Male cable
- Computer side of the cable kit consists of a HD15 Male cable, a USB A Male cable, 3.5mm Speaker/Microphone
- Molded, color-coded connectors

Package Includes

- 10-ft. (3.05 m) VGA/PS2/3.5mm All-in-1 KVM Cable Kit

Description

This PS/2 (All-in-One) KVM cable kit is designed to connect a PS/2 computer to a B006-VUA4-K-R KVM Switch. This premium All-in-1 cable provides superior performance and cable management. The KVM Switch side of the cable kit consists of a HD15 Male cable, plus two 3.5 mm stereo connectors. The computer side of the cable kit consists of a HD15 Male cable, 2 x PS/2 Male cables and 2 x 3.5 mm stereo connectors for speaker and microphone connections. All cables are manufactured from superior molded cabling with integral strain relief and foil shielding for maximum EMI/RFI protection.

Features

- Connects a USB Computer to B006-VUA4-K-R KVM Switch
- All-in-1 construction and slim size makes management and organization of cables much easier
- KVM Switch side of the cable kit consists of a HD15 Male cable, plus two 3.5mm stereo connectors
- Computer side of the cable kit consists of a HD15 Male cable, 2 x PS/2 Male cable, 2 x 3.5mm Speaker/Microphone
- Molded, color-coded connectors

Specifications

OVERVIEW	
UPC Code	037332154590
Accessory Type	Cable Kit
Technology	PS/2; VGA/SVGA; Stereo Audio
Accessory Class	KVM Switch Accessories
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	3.5MM (MALE)



Powering Business Worldwide



Side A - Connector 3	3.5MM (MALE)
Side B - Connector 1	HD15 (MALE)
Side B - Connector 3	3.5MM (MALE)
PHYSICAL	
Color	Gray
Cable Jacket Color	Gray
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.72
Shipping Weight (kg)	0.33
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.