

## 15-Pin SATA (Female) to 4-Pin (Male) Power Cable - 26 AWG, 6-in. (15.24 cm)

MODEL NUMBER: P944-06I



15-pin SATA (Female) to 4-Pin (Male) cable powers a Serial ATA hard drive from a standard Molex connection.

### Features

**15-Pin SATA to 4-Pin Molex Power Cable Needs Only an LP4 Power Supply Connection** This SATA 15-pin to 4-pin power cable connects any Serial ATA drive to any conventional LP4 internal connector. Ideal for desktops or servers equipped with a 2.5 in. or 3.5 in. SATA hard drive, this six-inch cable features one 4-pin Molex (LP4) male connector and one 15-pin SATA female power connector. It eliminates the need to upgrade the computer power supply for compatibility with newer SATA drives. The LP4 male pass through connector prevents having to take up a connector on the SATA drive.

## Specifications

OVERVIEW	
UPC Code	037332117779
Technology	SATA/eSATA
Country/Region	Global
INPUT	
Maximum Input Amps	0
CONNECTIONS	
Side A - Connector 1	15 PIN SATA POWER (FEMALE)
Side B - Connector 1	4 PIN (MALE)
PHYSICAL	
Color	Black; Red; Yellow

### Highlights

- Connects a SATA drive's 15-pin power port to a standard internal 4-pin Molex power supply
- Compatible with 2.5 in. and 3.5 in. SATA drives
- 4-Pin (Male) connector is pass through to avoid taking up a power supply connector

### Applications

- Use power from your computer via its LP4 connection to operate your SATA drive with a desktop computer or server containing multiple drives

### Package Includes

- P944-06I 15-Pin SATA (Female) to 4-Pin (Male) Power Cable, 6-in. (15.24 cm)



Powering Business Worldwide

TRIPP LITE  
SERIES

Number of Conductors	0
Wire Gauge (OD - mm <sup>2</sup> )	0
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	5.30 x 3.90 x 0.50
Shipping Dimensions (hwd / cm)	13.46 x 9.91 x 1.27
Shipping Weight (lbs.)	0.14
Shipping Weight (kg)	0.06
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
High Voltage	No
Locking Plug	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://triplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.