

## HDMI KVM Cable Kit - 4K HDMI, USB 2.0, 3.5 mm Audio (M/M), Black, 10 ft. (3.05 m)

MODEL NUMBER: P782-010-HA



Convenient 3-in-1 cable kit connects a computer or server with HDMI, USB and/or 3.5 mm ports to a compatible Tripp Lite KVM switch.

### Features

**10-ft. (3.05 m) Cables Connect Your Computer's HDMI, USB and Audio Ports to a Tripp Lite KVM Switch** This HDMI cable kit includes three cables for connecting your computer to a KVM switch.

Recommended for the Tripp Lite B024-HU08 and B024-HU16 KVM switches, the kit saves you money and cuts down on unnecessary clutter by combining necessary cables into one convenient bunch.

**HDMI** The HDMI cable lets you view the video content of your computer via the console's connected monitor. It supports Ultra HD resolutions up to 3840 x 2160 (@ 30 Hz) for crystal-clear 4K x 2K video.

**USB** The USB cable connects the KVM switch's USB-B port to your computer's USB-A port. It enables you to control all connected computers from one centralized keyboard/mouse, while also accessing external flash drives, printers, scanners or other devices connected to the switch's USB peripheral ports. The cable supports USB 2.0 data transfer speeds up to 480 Mbps.

**3.5 mm Audio** The 3.5 mm stereo cable connects external multimedia speakers, a microphone or headphones and share them between computers.

**Quality Construction Provides Superior Signal Transfer** Integral strain relief gives the cables extra flexibility, reduces stress, and helps the cables move freely without cracking or breaking loose from the connectors. Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded gold-plated connectors with gold-plated contacts provide maximum conductivity and minimum data loss to guarantee a clear transmission free of interference.

### Highlights

- Includes 10-ft. (3.05 m) HDMI, USB 2.0 A/B and 3.5 mm stereo audio cables in one kit
- Integral strain relief helps cables move freely without stress or cracking
- Foil/braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Gold-plated connectors and contacts for maximum conductivity and minimum data loss
- Supports UHD resolutions up to 3840 x 2160 (@ 30 Hz) for crystal-clear 4K x 2K video

### Applications

- Connect an HDMI monitor, keyboard/mouse and audio equipment, such as speakers or a microphone, to your Tripp Lite KVM switch

### System Requirements

- Computer with USB, HDMI and/or 3.5 mm ports
- Tripp Lite B024-HU08 or B024-HU16 KVM switch

### Package Includes

- P569-010 HDMI cable (M/M), 10 ft.
- U022-010 USB-A to USB-B cable (M/M), 10 ft.
- P312-010 3.5 mm audio cable (M/M), 10 ft.



## Specifications

OVERVIEW	
UPC Code	037332252654
Technology	HDMI; Stereo Audio; USB
VIDEO	
Max Supported Video Resolution	3840 X 2160 @ 30 Hz
AUDIO	
Audio Specification	Stereo Audio
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3
Cable Length (in.)	120
PHYSICAL	
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	14 TO 122 F (-10 TO 50 C)
Storage Temperature Range	5 TO 140 F (-15 TO 60 C)
Relative Humidity	0 TO 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side A - Connector 2	USB A (MALE)
Side A - Connector 3	3.5MM (MALE)
Side B - Connector 1	HDMI (MALE)
Side B - Connector 2	USB B (MALE)
Side B - Connector 3	3.5MM (MALE)
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>