

Plug-Lock Inserts (C20 power cord to C19 outlet), Black, 100 pack

MODEL NUMBER: PLC19BK



Highlights

- PLC19BK Plug-lock inserts keep C20 power cords connected to C19 outlets
- Prevents accidental disconnection of network hardware during routine rack maintenance
- Universal compatibility, no special cables, outlets or special PDU hardware required
- BLACK color inserts ship in packages of 100, more colors available

Package Includes

- 100 BLACK color C20 plug / C19 outlet compatible Plug-lock inserts

Description

Tripp Lite PLC19BK BLACK color Plug-lock inserts prevent accidental disconnection of C20 plug-in power cords from C19 output receptacles. IEC 60320 plug-in electrical cords are frequently loose-fitting and are often subject to accidental disconnection during routine network maintenance. To prevent critical equipment plugs from getting knocked loose, place a Plug-lock insert over any C20 input cord and connect it to any C19 outlet. The insert strengthens the connection of the plug to the outlet, keeping critical equipment plugged-in and running during routine rack access and maintenance. Plug-lock inserts provide a no-clutter alternative to common zip-tie cord retention schemes and a low cost answer to expensive proprietary locking plug and outlet hardware. PLC19BK Plug-lock inserts ship in packages of 100.

Features

- Tripp Lite PLC19BK Plug-lock inserts prevent accidental disconnection of C20 plug-in power cords from C19 outlets
- BLACK color PLC19BK inserts ship in packages of 100 pieces
- Corrects loose-fitting IEC60320 power connections that could lead to accidental disconnection of power cables
- Plug-lock inserts strengthen the connection of your C20 plug-in device to any C19 outlet, keeping vital network equipment plugged in and running during routine rack access and maintenance
- Universal compatibility ensures proper fit and enhanced plug retention when used with any standard C20 plug and C19 outlet combination; no proprietary cables or outlets required
- Simple installation, just place a Plug-lock insert over any C20 equipment power cord and plug it in
- Pull tabs enable safe retraction of the insert from powered C19 outlets
- Plug-lock inserts provide a no-clutter alternative to common zip-tie cord retention schemes and prevents reliance on lesser elegant remedies involving duct tape, electrical tape or super glue
- High strength PA66 nylon UL94 material with V2 flame rating

Specifications

OVERVIEW	
UPC Code	037332179739
Accessory Type	Plug-Lock Insert
Accessory Class	PDU Accessories
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	3.50 x 12.30 x 8.50
Shipping Dimensions (hwd / cm)	8.89 x 31.24 x 21.59
Shipping Weight (lbs.)	0.70
Shipping Weight (kg)	0.32
Unit Dimensions (hwd / in.)	1.290 x 1.420 x 1.060
Unit Dimensions (hwd / cm)	3.18 x 3.05 x 2.29
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty