

Serial ATA (SATA) Right-Angle Signal Cable (7Pin/7Pin-Down), 24-in.

MODEL NUMBER: P942-24I



Description

Tripp Lite's signal cables connect any high speed Serial ATA (SATA) device to a Serial ATA (SATA) controller. SATA delivers two significant benefits: it support much higher data transfer rates (up to 6.0 Gbps...backward compatible to 1.5Gbps), and the narrow cable design helps improve internal air flow. Perfect for the desktop or server that has multiple drives. These cables feature 7-pin straight/7-pin right-angle down connectors and offer easy installation.

Features

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Features 7Pin Straight and 7Pin Right-Angle Down connectors
- Angled connector ideal for situations in which space is at a premium, and reduces stress / excessive bending on the cable
- SATA III (6Gbps) / SATA II (3Gbps) / SATA I (1.5Gbps) Compliant
- Cable is shielded to protect against EMI/RFI

Specifications

Highlights

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Features 7Pin Straight and 7Pin Right-Angle Down connectors
- Angled connector ideal for situations in which space is at a premium, and reduces stress / excessive bending on the cable
- SATA III (6Gbps) / SATA II (3Gbps) / SATA I (1.5Gbps) Compliant
- Cable is shielded to protect against EMI/RFI

Applications

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Compatible with Serial ATA Hard Drives, Blu-ray/DVD/CD Drives and other Serial ATA devices

System Requirements

- SATA device
- SATA controller
- Data transfer rates are dependent upon the version of SATA supported by your device and controller

Package Includes

- Serial ATA (SATA) Right Angle Signal Cable (7Pin/7Pin-Down) 24-in.



OVERVIEW	
UPC Code	037332184405
Technology	SATA/eSATA
INPUT	
Cable Length (ft.)	2
Cable Length (m)	0.6
Cable Length (in.)	24
Cable Length (cm)	60.96
PHYSICAL	
Cable Outer Diameter (OD)	2.2 +/- 0.10 mm * 7.8 +/- 0.15 mm
Color	Red
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Weight (kg)	0.03
Shipping Weight (lbs.)	0.06
CONNECTIONS	
Side A - Connector 1	7 PIN SATA STRAIGHT (MALE)
Side B - Connector 1	7 PIN SATA (MALE) - RIGHT ANGLE DOWN
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>