

Serial ATA (SATA) Right Angle Signal Cable (7Pin-Up/7Pin-Down), 19-in.

MODEL NUMBER: P943-19I



Highlights

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Support data transfer rates of up to 6.0 Gbps
- Cable is shielded to protect against EMI/RFI

System Requirements

- Serial ATA device
- Serial ATA controller

Package Includes

- 19-in. Serial ATA Right Angle (SATA) Signal Cable 7Pin/7Pin, Up/Down

Description

Tripp Lite expands its line of hard drive cables with the introduction of our new line of serial ATA cables. The signal cables connect any high speed Serial ATA device to a Serial ATA controller. Serial ATA delivers two significant benefits: it support much higher data transfer rates (up to 6.0 Gbps...backward compatible to 1.5Gbps) and the narrow cable design helps improve internal air flow. Perfect for the desktop or server that has multiple drives. These cables feature 7-pin right-angle key up/7-pin right-angle key down female connectors and offer easy installation.

Features

- Connect your high-speed Serial ATA device to a Serial ATA controller
- Support data transfer rates of up to 6.0 Gbps
- Narrow cables design: 1) simplifies cable routing and installation 2) improves air flow within CPU (no more big ribbons blocking air movement) 3)Right Angle design for tight spaces
- Meets Serial ATA 1.0 standards, including Errata 029
- Cable is shielded to protect against EMI/RFI

Specifications

OVERVIEW	
UPC Code	037332120083
Technology	SATA/eSATA
CONNECTIONS	
Side A - Connector 1	7 PIN SATA (MALE) - RIGHT ANGLE UP
Side B - Connector 1	7 PIN SATA (MALE) - RIGHT ANGLE DOWN
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Color	Red
Cable Length (ft.)	1.6
Cable Length (m)	0.49
Cable Length (in.)	19
Cable Length (cm)	48.26
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.03
Shipping Weight (kg)	0.01
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.