

# 3-Outlet Power Strip - French Type E Outlets, 220-250V AC, 16A, 1.5 m Cord, Type E Plug, White

MODEL NUMBER: PS3F15



3-outlet power strip distributes electricity to home and office electronics, including computers, power tools and appliances.

## Features

**24 cm Power Strip Delivers Electricity to 3 Devices at the Same Time** Compatible with standard electrical equipment, this Protect It!® power strip features three French Type E outlets and a durable white plastic housing. It is ideal for powering almost anything with a compatible plug, including computers and mobile devices to appliances and power tools.

**Designed to Give You Flexibility in Placing the Power Strip Where It's Most Needed** The power strip features a space-saving right-angle Type E plug that helps you connect to a wall outlet located behind furniture that is placed flush against the wall. The plug is attached to a 1.5-meter power cord, which gives you more choices in placing the power strip away from the connected AC outlet.

**Vertical or Horizontal Mounting for Desks and Workbenches** Keyhole-shaped mounting slots on the back of the power strip allow you to permanently install it on any flat surface, including walls, with user-supplied hardware.

**Premium Safety Features Designed for Protecting Your Valuable Equipment** The PS3F15 features an on/off switch that provides one-touch control over all connected devices. In the event of an overload, a 16-amp circuit breaker immediately shuts down the power strip to prevent equipment damage.

## Specifications

OVERVIEW	
UPC Code	037332251541
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)

## Highlights

- 3 French Type E outlets distribute power to appliances, tools and other electronics
- Right-angle Type E plug permits connection in confined or hard-to-reach spaces
- 24 cm plastic housing designed to withstand the rigors of everyday use
- Rear keyhole slots enable mounting to desk or workbench for easy access to outlets
- 16A circuit breaker shuts down all outlets for safety in case of overload

## Applications

- Distribute power to computer equipment and other devices in an office, workbench, retail or telecom environment
- Mount a power strip to the edge of a desk or workbench for easy access to outlets

## Package Includes

- PS3F15 3-Outlet Power Strip, French Type E Outlets, White



Powering Business Worldwide



Voltage Compatibility (VAC)	220-250
Input Plug Type	French
Input Cord Length (ft.)	4.9
Right-Angle Plug	Yes
Input Cord Length (m)	1.49
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(3) French/Belgian
Circuit Breaker (amps)	13
Overload Protection	Combo power switch and circuit breaker
Outlet Orientation	Right-angled
Right-Angle Outlets	Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Switches	Two position power switch
<b>SURGE / NOISE SUPPRESSION</b>	
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Color	White
Material of Construction	Plastic
Power Cord Color	White
Housing Color	White
Mounting Holes or Slots	Yes
Receptacle Color	White
Shipping Dimensions (hwd / in.)	9.60 x 2.90 x 2.00
Shipping Dimensions (hwd / cm)	24.38 x 7.37 x 5.08
Shipping Weight (lbs.)	0.75
Shipping Weight (kg)	0.34



Powering Business Worldwide



Unit Dimensions (hwd / in.)	9.600 x 2.800 x 1.900
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
Built-In Circuit Breaker	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.