

5-Outlet Power Strip with USB Charging - French Type E Outlets, 220-250V, 16A, 3 m Cord, Type E Plug, White

MODEL NUMBER: PS5F3USB



5-outlet power strip with USB-A ports distributes electricity to home and office electronics and charges your mobile devices.

Features

43 cm Power Strip Delivers Electricity to 5 Devices at the Same Time Compatible with standard electrical equipment, this Protect It!® power strip features five French Type E outlets and a durable white plastic housing. It is ideal for powering almost anything with a compatible plug, including computers and mobile devices to appliances and power tools.

Charges 2 Mobile Devices with 2.1A of Shared Power In addition to AC outlets, this power strip provides USB charging for up to two mobile devices, including smartphones, tablets and e-readers. The USB-A ports eliminate the need for AC adapters for charging cords, leaving outlets available for AC equipment.

Designed to Give You Flexibility in Placing the Power Strip Where It's Most Needed The power strip features a space-saving right-angle Type E plug that helps you connect to a wall outlet located behind furniture that is placed flush against the wall. The plug is attached to a 3-meter power cord, which gives you more choices in placing the power strip away from the connected AC outlet.

Premium Safety Features Designed for Protecting Your Valuable Equipment The PS5F3USB features an on/off switch that provides one-touch control over all connected devices. In the event of an overload, a 16-amp circuit breaker immediately shuts down the power strip to prevent equipment damage.

Specifications

OVERVIEW	
UPC Code	037332251497
Product Type	Power Strip
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle

Highlights

- 5 French Type E outlets distribute power to appliances, tools and other electronics
- Right-angle Type E plug permits connection in confined or hard-to-reach spaces
- 2 USB-A ports share 2.1A of power for charging phones, tablets and other mobile devices
- 43 cm plastic housing designed to withstand the rigors of everyday use
- 16A circuit breaker shuts down all outlets for safety in case of overload

Applications

- Distribute power to computer equipment and other devices in an office, workbench, retail or telecom environment
- Charge a smartphone and tablet without taking up available AC outlets

Package Includes

- PS5F3USB 5-Outlet Power Strip, French Type E Outlets, White



Powering Business Worldwide



INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Input Plug Type	French
Input Cord Length (ft.)	9.8
Right-Angle Plug	Yes
Input Cord Length (m)	2.99
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(5) French/Belgian
Circuit Breaker (amps)	16
Overload Protection	Combo power switch and circuit breaker
Outlet Orientation	Right-angled
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Two position power switch
CHARGING	
Number of Charging Ports	2
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(2) 2.1A
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	White



Powering Business Worldwide



Material of Construction	Plastic
Power Cord Color	White
Housing Color	White
Mounting Holes or Slots	Yes
Receptacle Color	White
Shipping Dimensions (hwd / in.)	17.00 x 3.50 x 2.40
Shipping Dimensions (hwd / cm)	43.18 x 8.89 x 6.10
Shipping Weight (lbs.)	1.80
Shipping Weight (kg)	0.82
Unit Dimensions (hwd / in.)	16.700 x 3.100 x 2.000
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.