

5-Outlet Power Strip - German Type F Schuko Outlets, 220-250V, 16A, 1.5 m Cord, Schuko Plug, White

MODEL NUMBER: **PS5G15**



5-outlet power strip distributes electricity to home and office electronics, including computers, power tools and appliances.

Features

33 cm Power Strip Delivers Electricity to 5 Devices at the Same Time Compatible with standard electrical equipment, this Protect It!® power strip features five Type F Schuko outlets and a durable white plastic housing. It is ideal for powering almost anything with a compatible plug, including computers and mobile devices to appliances and power tools.

Designed to Give You Flexibility in Placing the Power Strip Where It's Most Needed The power strip features a space-saving right-angle Schuko plug that helps you connect to a wall outlet located behind furniture that is placed flush against the wall. The plug is attached to a 1.5-meter power cord, which gives you more choices in placing the power strip away from the connected AC outlet.

Premium Safety Features Designed for Protecting Your Valuable Equipment The PS5G15 features a lighted on/off switch that provides one-touch control over all connected devices. In the event of an overload, a 16-amp circuit breaker immediately shuts down the power strip to prevent equipment damage. The high-impact plastic housing is designed for the rigors of everyday use.

Specifications

OVERVIEW	
UPC Code	037332251626
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-240

Highlights

- 5 Schuko outlets distribute power to appliances, tools, lighting and other electronics
- Right-angle Schuko plug permits connection in confined or hard-to-reach spaces
- 33 cm plastic housing designed to withstand the rigors of everyday use
- On/off switch gives you convenient one-touch control over all connected devices
- 16A circuit breaker shuts down all outlets for safety in case of overload

Applications

- Distribute power to computer equipment and other devices in an office, workbench, retail or telecom environment

Package Includes

- PS5G15 5-Outlet Power Strip, German Type F Schuko Outlets, White



Powering Business Worldwide



Input Plug Type	German
Input Cord Length (ft.)	4.9
Right-Angle Plug	Yes
Input Cord Length (m)	1.49
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(5) Schuko Type F
Circuit Breaker (amps)	16
Overload Protection	Combo power switch and circuit breaker
Outlet Orientation	Right-angled
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
Switches	Two position power switch
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	White
Material of Construction	Plastic
Power Cord Color	White
Housing Color	White
Mounting Holes or Slots	Yes
Receptacle Color	White
Shipping Dimensions (hwd / in.)	13.00 x 2.80 x 2.20
Shipping Dimensions (hwd / cm)	33.02 x 7.11 x 5.59
Shipping Weight (lbs.)	0.95
Shipping Weight (kg)	0.43
Unit Dimensions (hwd / in.)	13.000 x 2.800 x 2.000



Powering Business Worldwide



FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.