



Powering Business Worldwide

# Panel Extension Kit for RapidPod Aisle Containment System - 18”H x 48”W

MODEL NUMBER: RAPOD1848PAN



Durable aluminum panel adds length to your modular RapidPod Aisle Containment System for a customized fit.

## Features

### Modular Customization of Your RapidPod Aisle Containment System

This assembly panel extension kit adds length to your RapidPod® Aisle Containment System to ensure a perfectly customized fit. Built with robust aluminum extrusions and five secure attachment points, the panel and included hardware allow fast configuration and adjustment directly in the field. Transparent and semi-transparent panel options offer clear visibility, while the customizable design accommodates a wide range of gap sizes and irregular layouts. Fully compatible with both hot- and cold-aisle containment strategies, this panel extension kit ensures durability and stability in demanding environments.

## Highlights

- Built with durable aluminum extrusions with 5 secure attachment points
- Modular assembly allows for quick configuration and adjustment
- Allows a customizable application to seal gaps and irregular layouts
- Available in transparent or semi-transparent polycarbonate for visibility
- Fully compatible with both hot-aisle and cold-aisle containment strategies

## Package Includes

- Assembly panel, 18 x 48 in.
- Formed panel joiner bracket, 18 in.
- (10) Screws, 5/16-18

## Specifications

| OVERVIEW                                |  |
|---|--|
| UPC Code                                | 037332299949   |
| Aisle Containment System Component Type | Panel  |
| PHYSICAL                                |  |
| Color                                   | Silver   |
| Unit Dimensions (hwd / in.)             | 18.000 x 48.000 x 1.880                                  |
| Unit Dimensions (hwd / cm)              | 18H 48W  |
| Unit Weight (lbs.)                      | 1  |
| Unit Weight (kg)                        | 0.45   |
| Rack Compatibility                      | 300 mm (In-Row Cooler); 600 mm (Standard); 750 mm (Wide) |



Powering Business Worldwide

| FEATURES & SPECIFICATIONS           |                            |
|-------------------------------------|----------------------------|
| Built-in Cable Management           | No                         |
| STANDARDS & COMPLIANCE              |                            |
| Product Compliance                  | Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT                  |                            |
| Product Warranty Period (Worldwide) | 5-year limited warranty    |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.