

## UPS Replacement Battery Cartridge Kit (2 sets of 2) for select APC UPS

MODEL NUMBER: RBC11A



### Highlights

- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range

### Package Includes

- UPS battery replacement cartridge
- Instruction manual with installation, recycling and warranty information

### Description

Tripp Lite's premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery set is carefully configured to meet or exceed all of the original manufacturer specifications and ships pre-assembled and ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. Compatible with select UPS systems from APC and other major brands. See Tripp Lite's UPS replacement battery page to confirm compatibility and quantity required.

### Features

- Restores your UPS to its original runtime specifications
- Comes pre-assembled and ready for installation into your UPS system
- Reusable packaging holds expired batteries for recycling center delivery
- Compatible with many brands and models, including APC models SU1400XLNET, SU1400RMXLNET, SU2200, SU2200NET, SU2200RM, SU2200RMNET, SU2200RMXL, SU2200RMXLT, SU2200XLNET, SU2200XLNET, SU3000, SU3000NET, SU3000RM, SU3000RMNET, SU24XLBP, SU48XLBP, and SU48BP

## Specifications

OVERVIEW	
UPC Code	037332118455
BATTERY	
Typical Battery Lifespan	3 - 5 years, depending on host UPS operating conditions



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>PHYSICAL</b>	
Shipping Dimensions (hwd / cm)	67.84 x 23.50 x 43.82
Shipping Dimensions (hwd / in.)	26.71 x 9.25 x 17.25
Shipping Weight (kg)	26.31
Shipping Weight (lbs.)	58.00
Unit Dimensions (hwd / cm)	Includes 2 batteries; Each measures 16.669 x 14.922 x 17.78
Unit Dimensions (hwd / in.)	Includes 2 batteries; Each measures 6.5625 x 5.875 x 7
Unit Weight (kg)	26.31
Unit Weight (lbs.)	58
<b>ENVIRONMENTAL</b>	
Relative Humidity	0 - 95% non-condensing
Operating Elevation (ft.)	0 - 10,000 feet
Storage Elevation (ft.)	0 - 50,000 feet
Operating Elevation (m)	0-3000 m
Storage Elevation (m)	0 - 15,200 m
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>