

UPS Battery Replacement for Select SMART1200LCD, SMART1500LCD, SMART1500LCDXL, SMX1500LCD UPS Systems

MODEL NUMBER: RBC1500



UPS backup battery replacement breathes new life into select Tripp Lite UPS systems whose internal batteries are expired or weak.

Features

UPS Replacement Battery Cartridge for Select Tripp Lite UPS Systems This UPS backup battery replacement is compatible with Tripp Lite's SMART1200LCD, SMART1500LCD, SMART1500LCDXL and SMX1500LCD UPS systems—the versions equipped with battery access doors only. Earlier versions of these models without a battery door are not compatible with the RBC1500. Please verify UPS compatibility as labeled on the UPS prior to ordering.

Carefully Screened and Certified Built to function in a wide range of operating temperatures, the RBC1500 has been carefully screened and certified to restore your UPS system's runtime performance to its original specifications.

Ready for Immediate Installation The leakproof, no-maintenance RBC1500 comes pre-assembled and pre-wired for quick and easy installation in your UPS system with battery access door. Reusable packaging holds expired batteries for delivery to the nearest recycling center.

Highlights

- Replacement battery backup for select battery-door-equipped Tripp Lite UPS systems
- Carefully screened and certified to restore UPS runtime to original specs
- Leakproof internal battery requires no regular maintenance
- Ships fully assembled and ready for immediate installation to prevent downtime
- Reusable packaging allows you to easily send expired batteries to recycling center

Applications

- Replace the aging or expired internal battery in your Tripp Lite battery-door-equipped UPS system

System Requirements

- SMART1200LCD, SMART1500LCD, SMART1500LCDXL and SMX1500LCD UPS system equipped with battery access door

Package Includes

- RBC1500 UPS Battery Replacement (pre-assembled battery pack with 2 12V batteries)

Specifications



UPC Code	037332214706
BATTERY	
DC System Voltage (VDC)	24
Typical Battery Lifespan	3 to 5 years typical, depending on UPS operating conditions
PHYSICAL	
Shipping Dimensions (hwd / in.)	6.50 x 8.07 x 12.60
Shipping Weight (kg)	6.53
Unit Dimensions (hwd / cm)	6.71 x 15.29 x 20.09
Unit Dimensions (hwd / in.)	2.64 x 6.02 x 7.91
Unit Weight (kg)	5.33
Unit Weight (lbs.)	11.75
WARRANTY	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>