

## UPS Replacement Battery Cartridge for SUINT1500LCD2U UPS System, 36V

MODEL NUMBER: RBC36S



UPS backup battery replacement breathes new life into a Tripp Lite UPS system suffering from expired or weak internal batteries.

### Features

#### UPS Replacement Battery Cartridge for SUINT1500LCD2U UPS System

This UPS backup battery replacement is carefully screened and certified to meet or exceed original specifications. The leakproof, no-maintenance RBC36S comes pre-assembled and pre-wired as three 12V batteries for quick and easy installation in your SUINT1500LCD2U. It functions within a wide range of operating temperatures. A sensor automatically informs the UPS that the battery has been replaced, so the UPS can reset the battery age. Reusable packaging allows you to easily send expired batteries to a recycling center.

### Highlights

- Replacement battery backup for SUINT1500LCD2U UPS system
- Carefully screened and certified to restore UPS runtime to original specs
- Leakproof internal battery requires no regular maintenance
- Ships fully assembled and ready for immediate installation to prevent downtime
- Auto-detection sensor allows UPS to reset internal battery age

### Applications

- Replace the aging or expired internal battery in your Tripp Lite SUINT1500LCD2U UPS system

### System Requirements

- Compatible with SUINT1500LCD2U UPS system

### Package Includes

- RBC36S UPS Battery Replacement (pre-assembled battery pack with three 12V batteries)

## Specifications

OVERVIEW	
UPC Code	037332192677
BATTERY	
DC System Voltage (VDC)	36
Included Battery Set	Contains (3) 12V 9AH sealed lead acid batteries
Typical Battery Lifespan	3 to 5 years, depending on UPS operating conditions
PHYSICAL	
Shipping Dimensions (hwd / in.)	5.70 x 11.70 x 14.60
Shipping Weight (kg)	9.00
Unit Dimensions (hwd / in.)	2.640 x 8.300 x 12.040
Unit Dimensions (hwd / cm)	6.71 x 21.08 x 30.58



Powering Business Worldwide

TRIPP LITE  
SERIES

Unit Weight (lbs.)	19.84
Unit Weight (kg)	9.00
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.