

UPS Replacement 24VDC Battery Cartridge for select Tripp Lite SLT UPS

MODEL NUMBER: RBC24-SLT



Highlights

- Tripp Lite-certified premium battery cartridge
- Pre-assembled and wired battery kit offers simple installation
- Rugged leak-proof construction
- Maintenance free
- Wide operating temperature range

Package Includes

- One pre-assembled battery pack consisting of two 12V batteries

Description

Tripp Lite's premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original specifications, and ships ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. See Tripp Lite's UPS replacement battery web page to confirm compatibility and quantity required.

Compatible with Tripp Lite UPS Models SMART750SLT, SMX750SLT, SMART1050SLT, SMX1050SLT (versions with pre-assembled 2-battery cartridges only; see compatibility listing for non-assembled battery versions)

Features

- Restores UPS runtime performance to original specifications
- Comes pre-assembled and ready for installation
- Reusable packaging holds expired batteries for recycling center delivery

Specifications

OVERVIEW	
UPC Code	037332127143
BATTERY	
DC System Voltage (VDC)	24
Included Battery Set	Contains (2) 12V 9AH sealed lead acid batteries
Typical Battery Lifespan	3-5 years, depending on UPS operating conditions
PHYSICAL	

Shipping Dimensions (hwd / in.)	4.60 x 6.30 x 11.50
Shipping Dimensions (hwd / cm)	11.68 x 16.00 x 29.21
Shipping Weight (lbs.)	13.50
Shipping Weight (kg)	6.12
Unit Dimensions (hwd / in.)	4.000 x 5.000 x 6.000
Unit Dimensions (hwd / cm)	10.2 x 12.7 x 15.2
Unit Weight (lbs.)	12.4
Unit Weight (kg)	5.62
ENVIRONMENTAL	
Relative Humidity	0-95% NON-CONDENSING
Operating Elevation (ft.)	0-10,000 FEET
Storage Elevation (ft.)	0-50,000 FEET
Operating Elevation (m)	0-3000 m
Storage Elevation (m)	0 - 15,200 m
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty