

## UPS Replacement 36VDC Battery Cartridge for select Tripp Lite SLT UPS

MODEL NUMBER: RBC36-SLT



### Highlights

- Tripp Lite-certified premium battery cartridge
- Pre-assembled and wired battery kit offers simple installation
- Rugged leak-proof construction
- Maintenance free
- Wide operating temperature range

### Package Includes

- One pre-assembled battery pack consisting of three 12V batteries

### Description

Tripp Lite's premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original specifications, and ships ready for installation into your UPS system.

Reusable packaging holds expired batteries for recycling center delivery. See Tripp Lite's UPS replacement battery web page to confirm compatibility and quantity required.

Compatible with Tripp Lite models SMART1500, SMART1500SLT, SMX1500SLT (versions with pre-assembled 3-battery cartridges only; see compatibility listing for non-assembled battery versions)

### Features

- Restores UPS runtime performance to original specifications
- Comes pre-assembled and ready for installation
- Reusable packaging holds expired batteries for recycling center delivery

## Specifications

OVERVIEW	
UPC Code	037332127136
BATTERY	
DC System Voltage (VDC)	36
Included Battery Set	Set of 3 pre-assembled 12V batteries
Typical Battery Lifespan	3-5 years, depending on UPS operating conditions



<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	4.60 x 6.50 x 11.40
Shipping Dimensions (hwd / cm)	11.68 x 16.51 x 28.96
Shipping Weight (lbs.)	19.30
Shipping Weight (kg)	8.75
Unit Dimensions (hwd / in.)	4 x 6 x 7.5
Unit Dimensions (hwd / cm)	10.16 x 15.2 x 19.1
Unit Weight (lbs.)	18.8
Unit Weight (kg)	8.53
<b>ENVIRONMENTAL</b>	
Relative Humidity	0-95% NON-CONDENSING
Operating Elevation (ft.)	0-10,000 FEET
Storage Elevation (ft.)	0-50,000 FEET
Operating Elevation (m)	0-3000 m
Storage Elevation (m)	0 - 15,200 m
<b>CERTIFICATIONS</b>	
Certifications	RoHS compliant
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>