

# UPS Replacement Battery Cartridge (Set of 16 Batteries) for Select Tripp Lite SmartOnline UPS Systems, 192VDC, 3U

MODEL NUMBER: RBC58-3US



UPS backup battery replacement breathes new life into a Tripp Lite UPS system suffering from expired or weak internal batteries.

## Features

### UPS Replacement Battery Cartridge for Select Tripp Lite UPS Systems

This premium set of 16 pre-wired 12V 5Ah batteries (two 96V battery trays) is designed for Tripp Lite UPS models specifying its use (see *System Requirements* below for a list). The RBC58-3US has been carefully screened and certified to meet or exceed original runtime specifications. The leakproof, no-maintenance backup battery comes pre-assembled for quick installation in your UPS system without potentially costly downtime, and it operates within a wide range of temperatures. Reusable packaging makes it easy for you to send the expired batteries to a recycling center.

## Highlights

- Maintenance-free battery backup for select UPS systems (see *System Requirements*)
- Carefully screened and certified to meet or exceed original UPS specs
- Reusable packaging holds expired batteries for recycling center delivery
- Ships fully assembled and ready for immediate installation to prevent downtime

## System Requirements

Designed for use with the following UPS systems and external battery packs:

- UPS Models with Built-In Receptacles: SU5KRT3UHV, SU5KRT3UX, SU5KRT3UG, SU5KRT3UHW, SU5KRT3UTF, SU6KRT3UHV, SU6KRT3UTF, SU6KRT3UX, SU6KRT3UG, SU6KRT3UHW
- UPS Models with a Detachable Bypass Power Distribution Module: SU5KRT3UHVMB, SU5KRT3UTFMB, SU5KRT3UGMB, SU5KRT3UHWMB, SU6KRT3UHVMB, SU6KRT3UHWMB, SU6KRT3UTFMB, SU6KRT3UGMB, SU6KRT3UHWMB, SU6KRT3UXMB
- External Battery Packs: BP192V12RT3US

## Package Includes

- RBC58-3US UPS Battery Replacement Cartridge (16 pre-wired batteries)
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332251275
BATTERY	
DC System Voltage (VDC)	192



Typical Battery Lifespan	3 to 5 years, depending on UPS operating conditions
<b>PHYSICAL</b>	
Unit Dimensions (hwd / in.)	3.74 x 4.7 x 22.54
Unit Dimensions (hwd / cm)	21.2 x 18 x 14
Unit Weight (lbs.)	71.4
Unit Weight (kg)	32.39
Rack Units	3
<b>ENVIRONMENTAL</b>	
Relative Humidity	0-95% non-condensing
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>