

UPS Replacement Battery Cartridge for select APC UPS, 16.9 lbs (7.6 kgs)

MODEL NUMBER: RBC6A



Highlights

- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range

Package Includes

- UPS battery replacement cartridge
- Instruction manual with installation, recycling and warranty information

Features

- Restore your UPS to its original runtime specifications
- Comes pre-assembled and ready for installation into your UPS system
- Reusable packaging holds expired batteries for recycling center delivery
- Compatible with many brands and models, including APC models BP1000, SUVS1000, SU1000, SU1000NET, SU1000RM, SU1000RMNET, and SUA1000

Specifications

| OVERVIEW | |
|---------------------------------|---------------------------------------------------------|
| UPC Code | 037332118424 |
| BATTERY | |
| Included Battery Set | Contains (2) 12V 11AH sealed lead acid batteries |
| Typical Battery Lifespan | 3 - 5 years, depending on host UPS operating conditions |
| PHYSICAL | |
| Shipping Dimensions (hwd / cm) | 15.24 x 19.05 x 30.48 |
| Shipping Dimensions (hwd / in.) | 6.00 x 7.50 x 12.00 |
| Shipping Weight (kg) | 8.62 |
| Shipping Weight (lbs.) | 19.00 |
| Unit Dimensions (hwd / cm) | 9,4 x 19,5 x 14,9 |



| | |
|-----------------------------------------|---------------------------|
| Unit Dimensions (hwd / in.) | 3.6875 x 7.6875 x 5.875 |
| Unit Weight (kg) | 7.67 |
| Unit Weight (lbs.) | 16.9 |
| ENVIRONMENTAL | |
| Relative Humidity | 0 - 95% non-condensing |
| Operating Elevation (ft.) | 0 - 10,000 |
| Storage Elevation (ft.) | 0 - 50,000 |
| Operating Elevation (m) | 0-3000 m |
| Storage Elevation (m) | 0 - 15,200 m |
| WARRANTY | |
| Product Warranty Period (U.S. & Canada) | 18-month limited warranty |
| Product Warranty Period (International) | 1-year limited warranty |
| Product Warranty Period (Mexico) | 1-year limited warranty |
| Product Warranty Period (Puerto Rico) | 1-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>