

4x 12V 9AH UPS Replacement Battery Cartridge Kit for Select Best, Powerware, Liebert and Other UPS

MODEL NUMBER: RBC54



Highlights

- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range

Package Includes

- 4 12V UPS replacement batteries
- Instruction manual with installation, recycling and warranty information

Description

These premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original manufacturer specifications and ships ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. Compatible with a wide variety UPS brands and models. See the UPS replacement battery web page to confirm compatibility and quantity required.

Features

- Restores UPS runtime performance to its original runtime specifications
- Reusable packaging contains expired batteries for recycling center delivery
- Compatible with a variety of UPS brands

Specifications

OVERVIEW	
UPC Code	037332118691
BATTERY	
Included Battery Set	Contains (4) 12V 9AH sealed lead acid batteries
Typical Battery Lifespan	3 - 5 years, depending on host UPS conditions
PHYSICAL	
Shipping Dimensions (hwd / in.)	6.80 x 7.00 x 13.70
Shipping Dimensions (hwd / cm)	17.27 x 17.78 x 34.80



Powering Business Worldwide



Shipping Weight (lbs.)	26.80
Shipping Weight (kg)	12.16
Unit Dimensions (hwd / in.)	4.000 x 2.500 x 6.000
Unit Dimensions (hwd / cm)	Set of 4 batteries; Each battery measures 9.4 x 6.4 x 14.9
Unit Weight (lbs.)	6
Unit Weight (kg)	2.72
ENVIRONMENTAL	
Relative Humidity	0 - 95% non-condensing
Operating Elevation	0-10000 ft. (0-3000 m)
Storage Elevation (ft.)	0 - 50,000
Storage Elevation (m)	0 - 15,200 m
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.