

UPS Replacement Battery Cartridge Kit for select Tripp Lite, Best, Powerware, Liebert and other UPS

MODEL NUMBER: RBC54



Highlights

- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range

Package Includes

- 4 12V UPS replacement batteries
- Instruction manual with installation, recycling and warranty information

Description

Tripp Lite's premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original manufacturer specifications and ships ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. Compatible with a wide variety of UPS brands and models. See Tripp Lite's UPS replacement battery web page to confirm compatibility and quantity required.

Features

- Restores UPS runtime performance to its original runtime specifications
- Reusable packaging contains expired batteries for recycling center delivery
- Compatible with a variety of UPS brands

Specifications

OVERVIEW	
UPC Code	037332118691
BATTERY	
Included Battery Set	Contains (4) 12V 9AH sealed lead acid batteries
Typical Battery Lifespan	3 - 5 years, depending on host UPS conditions
PHYSICAL	
Shipping Dimensions (hwd / cm)	17.27 x 17.78 x 34.80



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / in.)	6.80 x 7.00 x 13.70
Shipping Weight (kg)	12.16
Shipping Weight (lbs.)	26.80
Unit Dimensions (hwd / cm)	Set of 4 batteries; Each battery measures 9.4 x 6.4 x 14.9
Unit Dimensions (hwd / in.)	Set of 4 batteries; Each battery measures 3.6875 x 2.5 x 5.875
ENVIRONMENTAL	
Relative Humidity	0 - 95% non-condensing
Operating Elevation (ft.)	0 - 10,000
Storage Elevation (ft.)	0 - 50,000
Operating Elevation (m)	0-3000 m
Storage Elevation (m)	0 - 15,200 m
WARRANTY	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>