

Replacement Battery Cartridge for Select 72V Tripp Lite SmartOnline UPS Systems

MODEL NUMBER: RBC72S



Extends the battery life of select Tripp Lite SmartOnline UPS systems.

Description

The Tripp Lite RBC72S Replacement Battery Cartridge breathes new life into select Tripp Lite UPS systems whose internal batteries are expired or not working. Built to function in a wide range of operating temperatures, the RBC72S has been carefully screened and certified to restore your UPS system's runtime performance to its original specifications. The leakproof, no-maintenance RBC72S comes preassembled and prewired for quick and easy installation in your UPS system. Reusable packaging holds expired batteries for delivery to the nearest recycling center. Compatible with Tripp Lite's SU3000RTL2U (LED display to the right of front bezel), SU3000RTLCD2U, SU3000LCD2UHV, SUI3000LCD2U, SUI3000RTL2U (LED display to the right of front bezel) and other models recommending its use.

Features

Replacement Internal Battery for Select Tripp Lite UPS Systems

- Screened and certified to restore UPS system's runtime performance to original specs
- Compatible with Tripp Lite's SU3000RTLCD2U, SU3000LCD2UHV, SUI3000LCD2U and other models recommending its use
- Preassembled and prewired for immediate installation
- Designed for a wide range of operating temperatures
- Rugged leakproof construction
- No maintenance required
- Reusable packaging for delivering expired batteries to recycling center

Specifications

OVERVIEW

Highlights

- Replacement internal battery for select Tripp Lite UPS systems
- Rugged leakproof construction
- No maintenance required
- Wide range of operating temperatures
- Preassembled and prewired for immediate installations

Package Includes

- RBC72S Replacement 72V Battery Cartridge



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332189172
BATTERY	
DC System Voltage (VDC)	72
Included Battery Set	Contains (6) 12V 9AH sealed lead acid batteries
Typical Battery Lifespan	3 to 5 years, depending on UPS operating conditions
PHYSICAL	
Shipping Dimensions (hwd / cm)	9.60 x 23.01 x 49.02
Shipping Dimensions (hwd / in.)	3.78 x 9.06 x 19.30
Shipping Weight (kg)	18.20
Shipping Weight (lbs.)	40.12
Unit Dimensions (hwd / cm)	6.76 x 21.18 x 45.49
Unit Dimensions (hwd / in.)	2.66 x 8.34 x 17.91
Unit Weight (kg)	16.90
Unit Weight (lbs.)	37.26
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
Operating Elevation (ft.)	10,000 ft.
Storage Elevation (ft.)	10,000 ft.
Operating Elevation (m)	3,000 m
Storage Elevation (m)	3000 m
WARRANTY	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>