



Powering Business Worldwide

# SCSI/Fibre Channel - 24-in. Internal SCSI Ribbon Cable 3Conn 50SOK

MODEL NUMBER: **S004-24I**



### Highlights

- Premium cabling

### System Requirements

- Narrow SCSI controller
- Narrow SCSI device

### Package Includes

- 24 inch internal SCSI ribbon cable 3Conn 50SOK

### Description

Tripp Lite's internal 24in (2ft) 50pin SCSI ribbon cable has 3 connectors and is used to connect 50pin internal devices. This is the internal 50-pin ribbon cable required for narrow and wide SCSI applications (sometimes called SCSI-1 or SCSI-2). Perfect for internal CD-ROM drives and hard drives. Our products are fully tested and certified to meet or exceed applicable industry standards. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

### Features

- 24-in. long
- Three 50SOK(female) narrow SCSI connectors
- Lifetime warranty
- Internal 24in 50pin SCSI ribbon cable with 3 connections used to connect 50pin internal devices
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest ultra 320 to legacy SCSI-1 and every combination in between
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

## Specifications

OVERVIEW	
UPC Code	037332013743
Drives Supported	2
Technology	Ribbon/Internal; SCSI
CONNECTIONS	
Side A - Connector 1	50 SOCKET IDC (FEMALE)



Powering Business Worldwide

Side B - Connector 1	50 SOCKET IDC (FEMALE)
<b>PHYSICAL</b>	
Color	Gray
Cable Length (ft.)	2
Cable Length (m)	0.61
Cable Length (in.)	24
Shipping Dimensions (hwd / in.)	6.75 x 4.00 x 0.75
Shipping Dimensions (hwd / cm)	17.14 x 10.16 x 1.90
Shipping Weight (lbs.)	0.19
Shipping Weight (kg)	0.09
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.