

## SCSI/Fibre Channel - Passive External SCSI Terminator C50Male/Female Feed-Thru

MODEL NUMBER: **S118-000**



### Highlights

- Active terminators include a voltage regulator circuit to compensate for fluctuations in the host adapter

### System Requirements

- Any external use on a SCSI chain where a Cen50 Male terminator is required

### Package Includes

- Passive External SCSI Terminator C50Male/Female Feed-Thru

### Description

Tripp Lite's feed-thru C50 passive terminator is the one for all of your external SCSI II applications. Used with SCSI devices which have a C50 female port. Tripp Lite's passive terminators provide the clearest data signal maximizing signal integrity. Supports fast and Ultra single ended devices at 10 or 20 Mbps. Passive terminators do not have a voltage regulator circuit to compensate for fluctuations in the host adapter. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

### Features

- Passive terminators do not have a voltage regulator circuit to compensate for fluctuations in the host adapter
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

## Specifications

OVERVIEW	
UPC Code	037332013866
PHYSICAL	
Shipping Dimensions (hwd / in.)	6.75 x 4.00 x 0.75
Shipping Dimensions (hwd / cm)	17.14 x 10.16 x 1.90
Shipping Weight (lbs.)	0.14



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Shipping Weight (kg)	0.06
<b>CONNECTIONS</b>	
Side A - Connector 1	CENTRONICS 50 (MALE)
Side B - Connector 1	CENTRONICS 50 (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Technology	Ribbon/Internal; SCSI
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>