



Powering Business Worldwide

Internal SCSI U2/160 SCSI-LVD/SE 4-Drive Ribbon Cable with Terminator (5xHD68 M), 45-in.

MODEL NUMBER: **S054-45I**



Highlights

- Cable includes Active T-Type LVD/SE terminator
- UL-rated Amphenol brand cable
- Connects up to 5 drives

System Requirements

- Wide SCSI controller card
- Internal SCSI drives and devices with HD68 Pin interface

Package Includes

- 45-in. internal U160 SCSI ribbon cable 5Conn HD68M 4 drive with terminator

Description

Introducing Tripp Lite's internal SCSI Ultra2/U160 4-drive LVD ribbon cable with an active U160 terminator. This cable measures 45 inches in length and is made with twist and flat cabling. Because the cable is backwards compatible, it will support SCSI 1,2 & 3 devices such as CD-ROMs and Hard Drives. All Tripp Lite SCSI products regardless of the SCSI generation meet the latest SCSI specifications of ANSI (American National Standards Institute).

Features

- Ribbon cable connects up to 4 internal SCSI drives/devices to your internal SCSI controller
- HD68 male connectors
- Cable includes active terminator
- UL rated twist and flat cable
- SCSI U160 cables include active terminators which compensate for impedance mismatches
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest ultra 320 to legacy SCSI-1 and every combination in between

Specifications

OVERVIEW	
UPC Code	037332096524
Drives Supported	4
CONNECTIONS	
Side A - Connector 1	INTERNAL HD68 (MALE)
Side B - Connector 1	INTERNAL HD68 (MALE)



Powering Business Worldwide

PHYSICAL	
Color	Gray
Cable Length (ft.)	3.8
Cable Length (m)	1.16
Cable Length (in.)	45
Shipping Dimensions (hwd / in.)	10.00 x 6.00 x 3.00
Shipping Dimensions (hwd / cm)	25.40 x 15.24 x 7.62
Shipping Weight (lbs.)	0.37
Shipping Weight (kg)	0.17
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.