

## SCSI Ultra2/U160/U320 LVD Cable (VHDCI toHD68 M/M), 10-ft.

MODEL NUMBER: **S455-010**



### Highlights

- Premium double-shielded cable
- Meets the most current SCSI specifications for high-speed devices

### System Requirements

- Any external SCSI device or host controller card requiring VHDCI68 or HD68 interface

### Package Includes

- 10-ft. SCSI U320/U160 LVD/SE cable, VHDCI68M to HD68M

### Description

Moving your network into the next phase of SCSI solutions? Look no further than Tripp Lite's brand of SCSI U320/U160 cables. Supports all legacy transfer rates including Ultra 320 . Multi-platform SCSI III external peripheral cable, offset VHDCI68M/HD68M. This 10ft cable is designed to connect two SCSI III (fast and wide) or SCSI II devices together. Manufactured using double shielded 34 twisted pair high impedance cable. Constructed with low-capacitance, impedance matched, 28 AWG, stranded, tinned copper cable with insulated in polypropylene.

### Features

- Supports all SCSI transfer rates through 320Mbps
- LVD/SE compliant
- Backwards compatibility with previous SCSI generations
- Double shielded (foil and braid)
- 34 twisted pair conductors
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between

## Specifications

| OVERVIEW   |              |
|------------|--------------|
| UPC Code   | 037332121349 |
| Technology | SCSI         |
| INPUT      |              |



|                                     |                           |
|-------------------------------------|---------------------------|
| Cable Length (ft.)                  | 10                        |
| Cable Length (m)                    | 3.1                       |
| <b>PHYSICAL</b>                     |                           |
| Color                               | Black                     |
| Shipping Dimensions (hwd / cm)      | 21.59 x 17.53 x 1.27      |
| Shipping Dimensions (hwd / in.)     | 8.50 x 6.90 x 0.50        |
| Shipping Weight (kg)                | 0.45                      |
| Shipping Weight (lbs.)              | 1.00                      |
| <b>CONNECTIONS</b>                  |                           |
| Side A - Connector 1                | VHDCI68 (MALE)            |
| Side B - Connector 1                | HD68 (MALE)               |
| <b>WARRANTY</b>                     |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>