

SmartRack 42U Value Series Standard-Depth Rack Enclosure Cabinet

MODEL NUMBER: SR2000



Description

Tripp Lite's SmartRack 42U Value Series Standard-Depth Rack Enclosure Cabinet is designed for secure, high density server and networking applications in IT environments. Designed with provisions to integrate cooling, power distribution and cable management, SmartRack enclosures make ideal homes for mission-critical equipment. Toolless mounting accessory slots allow quick installation of PDUs and vertical cable managers. Lightweight locking, modular doors and side panels provide safe, convenient service access. SmartRack enclosures support cooling, cable management, power distribution and monitoring features that keep critical servers and network equipment operating nonstop.

Features

- Ships fully assembled
- Ships with flat, locking, front and rear doors, full length side panels, and roof and bottom panels
- 2000 lb stationary / 1100 lb rolling load capacity
- Rear sets of equipment mounting rails adjust in 3/8" increments.
- Toolless accessory mounting slots for quick installation of compatible PDUs and vertical cable managers. Mounting slots are arranged in an industry-standard pattern compatible with a wide variety of accessories. Each slot can accommodate two vertical PDUs or cable managers side-by-side (four items per enclosure).
- Rack Enclosure includes mounting hardware of 40 pieces of M6 cage nuts and 40 pieces of M6 screws
- Textured powder coat finish for tough resistance to environmental concerns such as deployment in warehouses.
- Maximum usable internal depth of 35 inches/889 mm (front to rear rail).
- Compatibility with airflow optimization accessories as well as cable management accessories.

Highlights

- 42U SmartRack Economy Rack Enclosure Cabinet with doors, side, roof and bottom panels
- 4 interior vertical posts with unthreaded square hole openings
- 2000 lb stationary / 1100 lb rolling load capacity
- Standard 24" (600mm) width and 40" (1016 mm depth) for optimizing floor space
- Includes 40 pieces of M6 cage nuts and 40 pieces of M6 screws (equipment mounting hardware)

Package Includes

- SmartRack 42U Value Series Standard-Depth Rack Enclosure Cabinet
- (1) Key sets for front / rear doors, and side panels
- (40) M6 Cage Nuts
- (40) M6 Screws
- (40) M6 Nylon Washers
- (2) Stabilizer brackets
- Owner's Manual



Specifications

OVERVIEW	
UPC Code	037332188212
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Enclosure
PHYSICAL	
Color	Black
Maximum Device Depth (cm)	88.90
Maximum Device Depth (in.)	35
Maximum Device Depth (mm)	889
Minimum Device Depth (cm)	57.45
Minimum Device Depth (in.)	22.62
Minimum Device Depth (mm)	575
Rack Height	42U
Shipping Dimensions (hwd / cm)	210.01 x 65.40 x 115.57
Shipping Dimensions (hwd / in.)	82.68 x 25.75 x 45.50
Shipping Weight (kg)	99.52
Shipping Weight (lbs.)	219.40
Unit Dimensions (hwd / cm)	197.28 x 59.99 x 100
Unit Dimensions (hwd / in.)	77.67 x 23.62 x 39.37
Unit Weight (kg)	76.84
Unit Weight (lbs.)	169.4
Weight Capacity - Rolling (kg)	499
Weight Capacity - Rolling (lbs.)	1100
Weight Capacity - Stationary (kg)	907
Weight Capacity - Stationary (lbs.)	2000
Rack Depth	Standard
Number of Vertical Mounting Rails	4
STANDARDS & COMPLIANCE	
Certifications	RoHS; IP20 Protection Rating
Approvals	EIA/ECA-310-E
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	5-year limited warranty
----------------------------------------	-------------------------

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>