


SmartRack Colocation Kit for 42U Deep Rack Enclosures

MODEL NUMBER: SRCOLOKIT42UDP



Converts a standard 42U deep rack enclosure into a dual-compartment colocation rack cabinet.

Features

Converts Your 42U Deep Rack into Dual Deep Racks

The SRCOLOKIT42UDP turns a standard 42U single-compartment deep rack into a dual-compartment colocation rack, allowing two different users to occupy an equal amount of rack space. Allowing multiple tenants to share a single cabinet within a data center reduces cost and maximizes valuable space. All necessary mounting hardware is included in this colocation kit.

Keeps Servers and Other Equipment Secure

An included divider panel separates the two compartments. The rack's original front and rear doors are replaced by independently lockable doors, each with its own unique, user-settable combination lock to help prevent damage, tampering or theft. The perforated doors allow generous airflow from front to rear to help keep your equipment cool and functioning at its peak.

Extra Depth Offers More Installation Options

The SRCOLOKIT42UDP is deeper than a standard rack's 42 inches. At 46 inches (1168 millimeters) deep, this colocation kit can accommodate larger servers and other equipment of equivalent mass. It is compatible with Eaton's 42U deep rack enclosures, such as SR42UBDP.

Highlights

- Allows 2 different users to occupy their own half of a 42U deep rack enclosure
- Each half has its own unique combination lock to prevent unauthorized access
- 46 in. depth designed to accommodate servers and other larger equipment
- Includes divider panel, doors, roof panel and all necessary mounting hardware
- Compatible with Eaton's 42U deep rack enclosures, including SR42UBDP

System Requirements

Compatible with Eaton 42U deep rack enclosures, including SR42UBDP

Package Includes

- (4) Colocation doors
- (4) Hinge brackets
- Divider plate
- Roof panel
- (2) Cable channels
- (2) Cable channel plates
- Blocking plate
- (4) Divider plate brackets
- (2) M6 screws
- (8) M6 x 10 mm flat-head screws
- (8) M6 x 16 mm flat-head screws
- (4) M4 screws
- (8) Cone washers
- Assembly instructions

Specifications

OVERVIEW	
UPC Code	037332277015
Accessory Type	Mounting Accessories; Rackmount Kit
Accessory Class	Rack Accessories



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Material of Construction	Cold rolled steel with powder-coated finish
Unit Dimensions (hwd / in.)	24.210 x 47.240 x 11.810
Assembly Required	Yes
STANDARDS & COMPLIANCE	
Product Compliance	EIA/ECA-310-E; RoHS

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.