



Powering Business Worldwide

## Emergency Fallback Ventilation System for SRCOOL3KTP Air Conditioner

MODEL NUMBER: SRCOOLTMVENT



Vents hot air out of your rack enclosure through convection if the air conditioner stops cooling due to power failure.

### Features

#### Allows Hot Air Trapped Inside a Rack Enclosure to Vent Out During Power Emergencies

This SmartRack® emergency fallback ventilation system works in conjunction with the SRCOOL3KTP Top-of-Rack Precision Cooling Air Conditioner (sold separately) to help prevent rack equipment from overheating in case of a cooling system failure. If the SRCOOL3KTP malfunctions due to power failure, the SRCOOLTMVENT's embedded thermal sensor triggers a lid release, allowing the hot air within the rack to dissipate. An SNMP alert via the SRCOOL3KTP's remote management will notify you that the vent has opened.

#### Easy to Install with Included Hardware

The SRCOOLTMVENT inserts easily into the SRCOOL3KTP's reserved slot using the included mounting screws and can be retrofitted into existing installations. A 12V DC power supply is also included.

### Highlights

- Performs in conjunction with the SRCOOL3KTP top-of-rack air conditioner
- Keeps rack equipment safely functioning in case of temporary cooling loss
- Integrates with SRCOOL3KTP's remote management with no special configurations
- Easy to install with included hardware and external power supply

### System Requirements

Requires installation with SRCOOL3KTP air conditioner

### Package Includes

- Emergency vent assembly
- (6) Mounting screws
- External power supply (Input: 100–240V, 50/60 Hz, 1A; Output: 12V 2.5A)
- Installation instructions

## Specifications

OVERVIEW	
UPC Code	037332267238
Accessory Type	Duct Kit
Accessory Class	Cooling Accessories
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V, 50/60 Hz, 1A
AC Power Adapter Output Specs (V / A)	12V 2.5A



Powering Business Worldwide

AC Power Adapter Cord Length (ft.)	6
<b>POWER</b>	
Power Source Type	AC Adapter
<b>PHYSICAL</b>	
Material of Construction	Steel housing
Housing Color	Black
Unit Dimensions (hwd / in.)	3.440 x 22.320 x 11.850
Unit Dimensions (hwd / cm)	8.74 x 56.59 x 30.1
Unit Weight (lbs.)	17.2
Unit Weight (kg)	7.80
Mounting Details	Allows heat from the rack to escape through the SRCOOL3KTP by opening up the top of the cooler.
<b>STANDARDS &amp; COMPLIANCE</b>	
External Power Supply Certifications	UL
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.