


Toolless Horizontal 90-Degree T-Junction for Fiber Routing System, 240 mm (10 in.)

MODEL NUMBER: SRFC10JUNT



240 mm T-section turns a straight horizontal run in your fiber management system into a 90-degree horizontal branch.

Features

High-Impact PVC T-Junction Helps You Create 90-Degree Fiber Cable Routing Branches

The SmartRack® SRFC10JUNT connects to three channel sections or other fittings in your fiber routing system to create a 90-degree horizontal branch. Three of Tripp Lite's SRFC10CPL10 couplers (sold separately) are required to complete your installation. Made from durable, lightweight PVC material, this T-section connects using the couplers' included hardware to help keep your fiber optic cable bundles neat and organized. Screws tighten by hand with no tools required to complete a professional, finished look in your data center, network closet or industrial space.

Highlights

- Allows you flexibility in creating your custom fiber optic cable routing system
- Constructed from durable but lightweight PVC plastic
- Easy to install with your fiber routing system with no tools needed
- Requires 3 Tripp Lite SRFC10CPL10 couplers (sold separately)

Applications

- Create a fiber routing system along the wall or ceiling of your data center or network closet or across the tops of the rack enclosures

System Requirements

- 3 x SRFC10CPL10 couplers (sold separately)

Package Includes

- Horizontal 90° T-junction, 240 mm
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332240996
Product Type	Junction
Cable Management System Component Type	Junction
PHYSICAL	
Color	Yellow



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / in.)	19.20 x 15.30 x 5.10
Shipping Weight (kg)	1.75
Unit Dimensions (hwd / cm)	11.341 x 47.599 x 37.693
Unit Dimensions (hwd / in.)	4.645 x 18.740 x 14.840
Unit Weight (kg)	0.54
Unit Weight (lbs.)	1.2
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>