


Toolless Straight Channel Section for Fiber Routing System, 240 x 120 x 1220 mm (10 x 5 x 48 in.)

MODEL NUMBER: **SRFC10STR48**



Straight channel raceway carries fiber optic cables horizontally through the fiber management system in your data center or network closet.

Features

High-Impact PVC Channel Section Lets You Create Custom Fiber Cable Routing Schemes

The SmartRack® SRFC10STR48 is a straight channel section that carries fiber optic cables horizontally through your fiber routing system. Made from durable, lightweight PVC material, this straight section connects to other sections or fittings via Tripp Lite's SRFC10CPL10 couplers (sold separately) using their included hardware to help keep your fiber optic cable bundles neat and organized. Screws and nuts tighten by hand with no tools required to complete a professional, finished look in your data center, network closet or industrial space.

Highlights

- Allows you flexibility in creating your custom fiber optic cable routing system
- Constructed from durable but lightweight PVC plastic
- Easy to install with your fiber routing system with no tools needed
- Requires Tripp Lite SRFC10CPL10 couplers (sold separately)

Applications

- Create a fiber routing system along the wall or ceiling of your data center or network closet or across the tops of the rack enclosures

System Requirements

- Tripp Lite SRFC10CPL10 couplers (sold separately)

Package Includes

- Straight channel section, 240 x 120 x 1220 mm
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332240798
Product Type	Channel
Cable Management System Component Type	Channel
PHYSICAL	
Color	Yellow



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / in.)	7.48 x 13.78 x 51.10
Shipping Weight (kg)	5.40
Unit Dimensions (hwd / cm)	11.69 x 27.787 x 121.917
Unit Dimensions (hwd / in.)	4.606 x 10.940 x 47.999
Unit Weight (kg)	0.54
Unit Weight (lbs.)	1.20
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>