


Toolless Movable Waterfall Adapter Kit with 48 in. Pipe for Fiber Routing System, 130 mm

MODEL NUMBER: SRFC4WTRFL48



Movable exit maintains a proper bend radius for fiber optic cables that are routed over the side of your fiber management system.

Features

High-Impact PVC Waterfall Helps You Create Custom Fiber Cable Routing Schemes

The SmartRack® SRFC4WTRFL48 connects to a straight channel section or other fitting in your fiber routing system to allow cabling to cascade over the side. It's movable, so your fiber cables can leave or enter where needed with a proper bend radius that protects against signal loss and breakage. Made from durable, lightweight PVC material, the waterfall assembles using the included hardware to help keep your fiber optic cable bundles neat and organized. Screws tighten by hand with no tools required to complete a professional, finished look in your data center, network closet or industrial space. Corrugated plastic piping is included for guiding cabling directly into your rack.

Highlights

- Allows you flexibility in creating your custom fiber optic cable routing system
- Constructed from durable but lightweight PVC plastic
- Easy to install with your fiber routing system with no tools needed
- 48 in. corrugated PVC piping feeds cables into the top of a rack

Applications

- Create a fiber routing system along the wall or ceiling of your data center or network closet or across the tops of the rack enclosures

System Requirements

Any straight section from Tripp Lite's Fiber Routing System

Package Includes

- Waterfall adapter, 130 mm
- Cover
- (2) T-shaped screws
- (2) Twist nuts
- Corrugated pipe, 48 in.
- Pipe affixer
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332253675
Product Type	Waterfall
Cable Management System Component Type	Drop Out/Waterfall



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Yellow
Shipping Dimensions (hwd / in.)	6.30 x 10.00 x 12.20
Shipping Weight (kg)	0.68
Unit Dimensions (hwd / cm)	136.144 x 18.542 x 19.558
Unit Dimensions (hwd / in.)	53.600 x 7.300 x 7.700
Unit Weight (kg)	0.52
Unit Weight (lbs.)	1.140
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>