

Toolless Trumpet Drop-Out Kit for Fiber Routing System, 120 mm (5 in.)

MODEL NUMBER: SRFC5DROP



Raceway trumpet spillout narrows your fiber optic cables to a standard 2 in. bend radius when exiting a channel or vertical T.

Features

High-Impact PVC Drop-Out Helps You Create Custom Fiber Cable Routing Schemes

The SmartRack® SRFC5DROP limits the bend radius of your fiber optic cabling to two inches (50 mm) as it exits from a channel, horizontal T fitting or vertical T. A proper two-inch bend radius protects against signal loss and damage to the cables. Made from durable, lightweight PVC material, this trumpet drop-out connects using the included hardware to help keep your cable bundles neat and organized. Screws and nuts tighten by hand with no tools required to complete a professional, finished look in your data center, network closet or industrial space.

Specifications

OVERVIEW	
UPC Code	037332240903
Product Type	Dropout
Accessory Type	Cable Management Accessories
Cable Management System Component Type	Drop Out/Waterfall
PHYSICAL	
Color	Yellow
Shipping Dimensions (hwd / in.)	2.80 x 5.70 x 7.80
Shipping Weight (kg)	0.23
Unit Dimensions (hwd / in.)	4.920 x 7.000 x 2.800

Highlights

- Allows you flexibility in creating your custom fiber optic cable routing system
- Constructed from durable but lightweight PVC plastic
- Easy to install with your fiber routing system with no tools needed

Applications

- Create a fiber routing system along the wall or ceiling of your data center or network closet or across the tops of the rack enclosures

System Requirements

Requires a 5 in. or 120 mm wide section from Tripp Lite's Fiber Routing System

Package Includes

- Trumpet dropout, 120 mm
- (4) T-shaped screws
- (4) Twist nuts
- Installation guide



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Dimensions (hwd / cm)	12.5 x 17.78 x 7.11
Unit Weight (lbs.)	0.291
Unit Weight (kg)	0.13
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>