


Toolless 45-Degree Up/Down Ramp Kit for Fiber Routing System, 240 mm (10 in.)

MODEL NUMBER: SRFC10RAMP



240 mm ramps raise or lower the level of a straight horizontal run in your fiber management system.

Features

High-Impact PVC Ramps Help You Create Custom Fiber Cable Routing Schemes

The SmartRack® SRFC10RAMP connects to straight channel sections or other fittings in your fiber routing system to raise or lower it to a different level. Two of Tripp Lite's SRFC10CPL10 couplers (sold separately) are required to complete your installation. Made from durable, lightweight PVC material, these ramps connect using the included hardware to help keep your fiber optic cable bundles neat and organized. Screws tighten by hand with no tools required to complete a professional, finished look in your data center, network closet or industrial space.

Highlights

- Allows you flexibility in creating your custom fiber optic cable routing system
- Constructed from durable but lightweight PVC plastic
- Easy to install with your fiber routing system with no tools needed
- Requires 2 Tripp Lite SRFC10CPL10 couplers (sold separately)

Applications

- Create a fiber routing system along the wall or ceiling of your data center or network closet or across the tops of the rack enclosures

System Requirements

- 2 x SRFC10CPL10 couplers (sold separately)

Package Includes

- Down elbow, 45°
- Up elbow, 45°
- Coupler
- (8) Shank screws
- Installation guide

Specifications

| OVERVIEW | |
|--|--------------|
| UPC Code | 037332240958 |
| Product Type | Ramp |
| Cable Management System Component Type | Ramp |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| PHYSICAL | |
|-------------------------------------|-----------------------------|
| Color | Yellow |
| Shipping Dimensions (hwd / in.) | 6.50 x 10.10 x 11.80 |
| Shipping Weight (kg) | 1.27 |
| Unit Dimensions (hwd / cm) | 11.7983 x 47.5996 x 37.6936 |
| Unit Dimensions (hwd / in.) | 4.645 x 18.740 x 14.840 |
| Unit Weight (kg) | 0.54 |
| Unit Weight (lbs.) | 1.2 |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 5-year limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>