


# Toolless Movable Waterfall Adapter Kit for Fiber Routing System, 130 mm

MODEL NUMBER: SRFC4WTRFL



Movable exit maintains a proper bend radius for fiber optic cables that are routed over the side of your fiber management system.

### Features

#### High-Impact PVC Waterfall Helps You Create Custom Fiber Cable Routing Schemes

The SmartRack® SRFC4WTRFL connects to a straight channel section or other fitting in your fiber routing system to allow cabling to cascade over the side. It's movable, so your fiber cables can leave or enter where needed with a proper bend radius that protects against signal loss and breakage. Made from durable, lightweight PVC material, the waterfall assembles using the included hardware to help keep your fiber optic cable bundles neat and organized. Screws tighten by hand with no tools required to complete a professional, finished look in your data center, network closet or industrial space.

### Highlights

- Allows you flexibility in creating your custom fiber optic cable routing system
- Constructed from durable but lightweight PVC plastic
- Easy to install with your fiber routing system with no tools needed

### Applications

- Create a fiber routing system along the wall or ceiling of your data center or network closet or across the tops of the rack enclosures

### System Requirements

Any straight section from the SRFC family

### Package Includes

- Waterfall adapter, 130 mm
- Cover
- (2) T-shaped screws
- (2) Twist nuts
- Installation guide

## Specifications

OVERVIEW	
UPC Code	037332240873
Product Type	Waterfall
Accessory Type	Cable Management Accessories
Cable Management System Component Type	Drop Out/Waterfall
PHYSICAL	
Color	Yellow
Shipping Dimensions (hwd / in.)	6.30 x 7.08 x 8.07
Shipping Weight (kg)	0.43
Unit Dimensions (hwd / in.)	5.600 x 7.680 x 7.700
Unit Dimensions (hwd / cm)	14.224 x 19.507 x 19.558



Powering Business Worldwide



Unit Weight (lbs.)	0.602
Unit Weight (kg)	0.27
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.