

## Copper Bus Grounding Bar for 24U and 25U Racks

MODEL NUMBER: SRGROUND25



Half-length bus grounding bar attaches to your open frame rack or enclosure to provide ground contact for rack-mount equipment.

### Features

#### Provides Convenient Ground Contact for Your Rack-Mounted Equipment

This SmartRack® grounding bar is a thin strip of heavy-gauge solid copper that attaches to any EIA-standard 24U or 25U rack enclosure or open frame rack. Every other U space has a drilled and tapped hole to allow a ground wire jumper to be installed, providing convenient ground contact for standard rack equipment. The jumper then bridges to individual rack components, with grounding straps, allowing a direct path to ground, rather than going through surrounding equipment.

#### Easy to Install with All Hardware Included

You can mount the SRGROUND25 in any EIA-standard 24U or 25U rack enclosure or open frame rack. Either screw it into a rack enclosure using the included mounting hardware, or install it in an open frame rack with the included toolless mounting buttons. This copper grounding bar is ideal for large data centers that contain ground-sensitive equipment.

### Highlights

- Copper grounding bar provides ground contact for your rack-mount equipment
- Installs in your 24U or 25U enclosure or open frame rack with included hardware
- Recommended for large data centers that have ground-sensitive equipment
- Heavy-gauge copper construction with drilled and tapped hole in every other U space

### Applications

Provides convenient ground contact for standard rack-mount equipment in a 24U or 25U rack

### System Requirements

Fits into any standard 24U or 25U open frame rack or rack enclosure

### Package Includes

- Grounding bar with attached lug, 45 in.
- (2) Mounting buttons
- (13) Grounding straps
- (2) M4 self-tapping screws
- (13) M4 screws
- (13) Washers
- (2) Cage nuts
- (2) M6 x 12 screws
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332241474



<b>PHYSICAL</b>	
Shipping Dimensions (hwd / cm)	124.00 x 8.51 x 5.99
Shipping Dimensions (hwd / in.)	48.82 x 3.35 x 2.36
Shipping Weight (kg)	1.81
Shipping Weight (lbs.)	4.00
Unit Dimensions (hwd / cm)	114.808 X 1.588 X 0.635
Unit Dimensions (hwd / in.)	45.200 X 0.625 X 0.250
Unit Weight (kg)	1.36
Unit Weight (lbs.)	3.00
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>