

SmartRack 1U ESD Grounding Panel

MODEL NUMBER: SRGROUNDANELBC



Mounts to EIA-standard 19 in. rack to provide ground contact for ESD bands. Ideal for factories, warehouses and anywhere else static discharge could damage equipment.

Description

The SRGROUNDANELBC SmartRack 1U ESD Grounding Panel attaches to rack enclosures and open frame racks to provide ground contact and prevent static discharge. It's ideal for factories, warehouses and anywhere else static discharge could damage expensive and delicate electronic equipment. Compatible with all EIA-standard 19-inch racks, the panel includes grounding for both banana-plug and alligator-clip ESD bands. Ground wires are 48 inches for easy connection. All mounting hardware is included.

Features

Prevents Static Discharge While Handling Delicate Electronics

- Mounts to 1U of space in rack enclosures and open frame racks
- Ideal for factories, warehouses and anywhere else static discharge could damage equipment
- Compatible with EIA-standard 19 in. racks
- Provides ground contact for banana-plug and alligator-clip ESD bands
- 48 in. ground wires for easy connection
- Includes all mounting hardware

Specifications

OVERVIEW	
UPC Code	037332191731
Accessory Type	Grounding Bars & Panels
Accessory Class	Rack Accessories
PHYSICAL	
Shipping Dimensions (hwd / in.)	3.10 x 3.10 x 21.70

Highlights

- Mounts to rack enclosures and open frame racks
- Compatible with EIA-standard 19 in. racks
- Grounding for banana-plug and alligator-clip ESD bands
- 48 in. ground wires for easy connection
- Includes all mounting hardware

Package Includes

- SRGROUNDANELBC SmartRack 1U ESD Grounding Panel
- (2) M6 screws
- (2) M6 cage nuts
- (2) M6 cup washers



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / cm)	7.87 x 7.87 x 55.12
Shipping Weight (lbs.)	1.40
Shipping Weight (kg)	0.64
Unit Dimensions (hwd / in.)	1.720 x 2.000 x 19.000
Unit Dimensions (hwd / cm)	4.37 x 5.08 x 48.26
Unit Weight (lbs.)	0.50
Unit Weight (kg)	0.23
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.