

## SmartRack Copper Bus Grounding Bar

MODEL NUMBER: SRGROUND



### Highlights

- Attach to rack enclosure cabinets or open frame racks to provide ground contact
- Heavy-gauge solid copper
- All hardware is included

### Package Includes

- SRGROUND Copper Bus Grounding Bar
- (21) Grounding straps
- (3) Mounting buttons
- (21) M4 screws
- (21) Washers
- Owners Manual

### Description

The SRGROUND is a full-length (42U) bus grounding bar made from heavy-gauge solid copper that attaches to Rack Enclosure Cabinets or Open Frame Racks to provide convenient ground contact for standard rack-mount equipment. Every other U space has a drilled and tapped hole to allow a ground wire "jumper" to be installed. The jumper then bridges to the individual pieces of equipment with grounding straps, allowing a direct path to ground, rather than going through surrounding equipment. The SRGROUND can mount in an enclosure in two ways: it can be screwed into the Rack Enclosures (hardware included) or it can be installed using the toolless mounting buttons in the Open Frame Racks.

### Features

- Full length (42U) bus grounding bar made from heavy-gauge solid copper that attaches to Rack Enclosure Cabinets or Open Frame Racks to provide convenient ground contact for standard rack-mount equipment
- Every other U space has a drilled and tapped hole to allow a ground wire "jumper" to be installed
- The jumper then bridges to the individual pieces of equipment, with grounding straps, allowing a direct path to ground rather than going through surrounding equipment
- Can mount in a enclosure in two ways: it can be screwed into the Rack Enclosures (hardware included), or it can be installed using the tool less mounting buttons in the Open Frame Racks

## Specifications

OVERVIEW	
UPC Code	037332154811
Accessory Type	Grounding Bars & Panels
Accessory Class	Rack Accessories
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.40 x 3.60 x 78.50
Shipping Dimensions (hwd / cm)	6.10 x 9.14 x 199.39



Powering Business Worldwide

TRIPP LITE  
SERIES

Shipping Weight (lbs.)	5.50
Shipping Weight (kg)	2.49
Unit Dimensions (hwd / in.)	75.500 x 0.625 x 0.250
Unit Dimensions (hwd / cm)	191.77 x 1.59 x 0.63
Unit Weight (lbs.)	4
Unit Weight (kg)	1.81
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.