

SmartRack Locking Door Handle for Server Rack Cabinets - Front and Back Doors, SFIC Lock Core, 2 Keys

MODEL NUMBER: SRHANDLESFIC



Replacement lock handle kit allows facility and IT managers to designate authorized access to rack cabinets.

Features

Theft-Deterrent Replacement Handle Prevents Unauthorized Access to Your Rack Cabinet

This SmartRack replacement lock handle kit helps you securely store your valuable rack-mounted equipment to protect it from damage, tampering or theft. It's recommended for data centers, server rooms or network closets where you need your floor-standing rack enclosures to be protected from unauthorized access.

Swing Handles Come with SFIC Lock Core

The SRHANDLESFIC fits SmartRack enclosure door assemblies equipped with handles. Replacement swing handles for front and rear doors are included. They replace the rack cabinet's existing door handles using the included mounting hardware. The included keys fit SRHANDLESFIC locks only, allowing you to control who has access to internal equipment. The replaceable small format interchangeable core (SFIC) allows quick and convenient rekeying if access requirements change.

Highlights

- Replacement door lock fits SmartRack® floor-standing enclosures with door handles
- Secure locking lets facility and IT managers closely guard access to enclosure
- SFIC core allows fast and convenient rekeying when access requirements change
- Includes temporary SFIC core, mounting hardware and 2 keys specific to this model

System Requirements

SmartRack floor-standing enclosure with front and/or rear door handles

Package Includes

- (2) Locking handles
- (2) Keys
- Temporary SFIC core
- Mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332288929
Accessory Type	Handle Kit
Accessory Class	Rack Accessories
PHYSICAL	
Shipping Dimensions (hwd / in.)	6.77 x 3.22 x 2.05
Shipping Weight (kg)	0.20
Unit Dimensions (hwd / in.)	6.410 x 1.420 x 1.340



Powering Business Worldwide

TRIPP LITE
SERIES

FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	EIA/ECA-310-E; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.