

Butt-Splice Kit for Straight and 90-Degree Ladder Runway Sections - Hardware Included

MODEL NUMBER: SRLBUTTSPLICE



Easy-to-use butt-splice kit safely and securely connects 2 sections of cable management ladder end-to-end.

Features

Convenient Cable Ladder Connector Lengthens the Runway System in Your Data Center This SmartRack butt-splice kit creates a secure connection point between two sections of cable ladder to extend the cable runway system in your server room or data center. All mounting and installation hardware is included. The splice plates fit solid and tubular steel runway measuring 1.5 x 0.375 inches (38 x 9.5 millimeters). The SRLBUTTSPLICE is designed to connect SRCABLELADDER, SRCABLELADDER18, SRL90BEND12, SRL90BEND18 and other compatible straight and 90-degree ladder sections.

Highlights

- Securely connects cable management ladders outside rack enclosure or open frame rack
- Compatible with both straight and 90-degree-bend ladder sections
- Fits solid and tubular steel runway measuring 1.5 x 0.375 in.
- Works with all SmartRack® ladder system accessories and runways
- Includes all necessary mounting and installation hardware for immediate use

Applications

- Lengthen a ladder runway system outside your data center's rack enclosure or open frame rack

System Requirements

- Compatible with straight and 90-degree-bend ladder sections, including SRCABLELADDER, SRCABLELADDER18, SRL90BEND12, SRL90BEND18.

Package Includes

- (4) Splice plates
- (2) M10 bolts
- (2) M10 split lock washers
- (2) M10 hex nuts
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332214461
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.56 x 2.76 x 5.50
Shipping Dimensions (hwd / cm)	6.50 x 7.01 x 13.97



Powering Business Worldwide



Shipping Weight (lbs.)	0.96
Shipping Weight (kg)	0.44
Unit Dimensions (hwd / in.)	2.560 x 2.760 x 5.500
Unit Dimensions (hwd / cm)	6.6 x 7.11 x 13.97
Unit Weight (lbs.)	0.840
Unit Weight (kg)	0.38
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.