


Ceiling Center Support Kit for 18 in. Cable Runway, Straight and 90-Degree - Hardware Included

MODEL NUMBER: SRLCNTRSPPT18



Easy-to-connect ceiling support kit safely and securely creates a single point of attachment to simplify cable runway installation.

Features

Cable Ladder Center Support Kit Secures Your Data Center's Runway System to the Ceiling This SmartRack cable runway center support kit creates a single point of attachment from the ceiling of your server room or data center to a ladder section. All mounting and installation hardware is included, except for the threaded rod (because of variable ceiling heights) and appropriate fasteners to secure the durable steel wall bracket. The mounting surface must be able to support the combined equipment load safely. Be sure to use suitable mounting means when installing to cinder block, concrete, drywall or wooden studs. The SRLCNTRSPPT18 is designed for use with Tripp Lite's 18-inch (457-millimeter) SRCABLELADDER18, SRL90BEND18 and other compatible straight and 90-degree ladder sections.

Highlights

- Securely connects cable management ladders to the ceiling of your data center
- Compatible with both 18 in. (457 mm) straight and 90-degree-bend ladder sections
- Works with all 18 in. Tripp Lite SmartRack® ladder system accessories and runways

Applications

- Secure a ladder runway system from a rack enclosure or open frame rack to the ceiling of your data center or server room.

System Requirements

- Compatible with 18 in. (457 mm) straight and 90-degree-bend ladder sections, including Tripp Lite SRCABLELADDER18 and SRL90BEND18

Package Includes

- Center support bracket
- Threaded rod cover
- (2) 5/8-11 hex nuts
- (2) 5/8 lock washers
- (2) M8 J-bolts
- (2) M8 lock washers
- (2) M8 hex nuts
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332214591



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	3.56 x 6.10 x 50.04
Shipping Dimensions (hwd / in.)	1.40 x 2.40 x 19.70
Shipping Weight (kg)	0.68
Shipping Weight (lbs.)	1.50
Unit Dimensions (hwd / cm)	3.556 x 6.096 x 50.04
Unit Dimensions (hwd / in.)	1.40 x 2.4 x 19.70
Unit Weight (kg)	0.54
Unit Weight (lbs.)	1.20
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>