


SmartRack Enclosure Skirt Kit for Wide Server Racks, 750 mm Width

MODEL NUMBER: SRSKIRTWD



Blocks unwanted airflow beneath wide rack enclosures to improve cooling efficiency.

Features

Improves Cooling Efficiency and Optimizes Airflow in Your Wide Rack

This SmartRack® brush skirt kit blocks unwanted airflow under a wide rack cabinet. By segregating cold aisles from hot aisles, this easy-to-install brush strip helps you reduce operating costs, improve equipment performance and provide longer lifespans for rack-mounted networking components. It also prevents dust from infiltrating the rack's interior.

Installation Is Simple and Hassle-Free

This server rack skirt kit is compatible with wide rack cabinets, which measure 750 millimeters in width. All necessary mounting equipment is included. Just install the brush strip at floor level across the front or rear of the cabinet to prevent an air stream from forming between hot and cold aisles.

Highlights

- Compatible with 750 mm wide rack cabinets for blocking unwanted airflow
- Improves cooling efficiency by segregating hot aisles from cold aisles
- Hassle-free brush strip also prevents dust from getting inside the rack
- Includes all necessary installation hardware, so you can mount immediately

System Requirements

For use with 750 mm wide rack enclosures

Package Includes

- SRSKIRTWD Enclosure Skirt Kit, 750 mm Width
- Mounting hardware
- Installation instructions

Specifications

OVERVIEW	
UPC Code	037332283528
Accessory Type	Enclosure Skirt Kit
Accessory Class	Cooling Accessories
COOLING	
Cooling Type	Passive
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.75 x 30.31 x 0.59
Shipping Dimensions (hwd / cm)	7.00 x 77.00 x 1.50
Shipping Weight (lbs.)	0.78



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Weight (kg)	0.35
Unit Dimensions (hwd / in.)	2.514 x 29.500 x 0.394
Unit Dimensions (hwd / cm)	6.39 x 74.93 x 1
Unit Weight (lbs.)	1.5
Unit Weight (kg)	0.68
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.