

# SmartRack Thermal Duct Kit for SmartRack Enclosures

MODEL NUMBER: SRTHERMDUCT



Need to help your equipment perform at its peak while reducing your facility's cooling and energy cost? The SRTHERMDUCT kit can change a standard Tripp Lite SmartRack 42-48U enclosure into sealed passive cooling structure that allows heat that is exhausted from equipment to be vented upwards into the facility CRAC / HVAC air return system.

## Description

The SRTHERMDUCT Thermal Duct Kit can change a standard SmartRack 42-48U enclosure into a sealed passive cooling structure that allows heat built up inside a rack to be directed up and into the facility CRAC / HVAC return air system.

## Features

- Improves cooling efficiency of standard rack enclosures
- Adjustable roof-mount thermal duct connects to HVAC return air system
- Included gaskets and panels help seal enclosure for proper airflow management through thermal duct
- Compatible with standard 42-48U SmartRack Enclosures

## Specifications

OVERVIEW	
UPC Code	037332154903
Accessory Type	Duct Kit
Accessory Class	Rack Accessories
COOLING	
Cooling Type	Passive
PHYSICAL	
Housing Color	Black

## Highlights

- Improves cooling efficiency in standard rack enclosures
- Adjustable roof-mounted thermal duct moves air upward and out of the rack enclosure
- Compatible with standard 42-48U SmartRack Enclosures

## System Requirements

Standard 42-48U Rack Enclosure

## Package Includes

- Height-adjustable roof-mount thermal duct
- Roof-mount cable access panel
- Enclosure bottom
- Door gasket seals
- (16) Magnetic vinyl sheet rear door seals
- (4) M8 screws
- (4) M4 screws
- (16) M4 nuts
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

Roof	Thermal duct adjusts between 20.5-34.5 inches when assembled.
Shipping Dimensions (hwd / in.)	14.57 x 23.62 x 47.64
Shipping Dimensions (hwd / cm)	37.01 x 59.99 x 121.01
Shipping Weight (lbs.)	67.00
Shipping Weight (kg)	30.39
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.