


SmartRack 3U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Structured Wiring Enclosure with Adjustable Equipment Brackets

MODEL NUMBER: SRWF3UDG



3U wall-mount structured wiring enclosure with removable 1U shelves secures and organizes 19 in. rack equipment, as well as other equipment not typically stored in a rack, such as modems and routers.

Description

The SRWF3UDG SmartRack® 3U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Structured Wiring Enclosure is designed to house both regular rack equipment and other equipment not typically mounted in an EIA-standard 19-inch rack. This vertical equipment rack is recommended for wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need components to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the 3U rack cabinet has a maximum load capacity of 150 pounds.

The SRWF3UDG media enclosure includes two pre-installed, but removable, 1U shelves with adjustable metal equipment brackets that attach easily to the cabinet's square mounting holes. Just place your modem, router and other non-rack equipment on the brackets, and use the included thumbscrew to secure them to the rack. Four RJ45 jacks are built into the rack cabinet for connecting your devices to a network.

When the two shelves are removed, the low-profile rack can accommodate two 3U areas of rack-mount equipment, one above the other. The enclosure extends less than five inches from the wall, while housing equipment up to 16.5 inches deep, including network switches and patch panels.

The reversible front door locks securely with a built-in combination lock to help prevent damage, tampering or theft. The vented cabinet allows air to flow freely and keep equipment cool. Brush-strip cable plates on both sides allow easy cable routing while preventing dust from entering. The SRWF3UDG structured wiring cabinet comes fully assembled and ready to mount to the wall.

Features

Structured Wiring Enclosure Saves Valuable Workspace

- Ideal for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way
- Houses 19 in. rack equipment in two 3U areas of space (when pre-installed shelves are removed)
- Low-profile vertical-mount cabinet extends less than 5 in. from the wall while housing equipment up to

Highlights

- 2 removable 1U shelves with adjustable metal brackets secure non-rack equipment
- Houses 2 areas of 3U of rack equipment up to 16.5 in. deep (when 1U shelves are removed)
- Structured wiring cabinet extends less than 5 in. from wall with max capacity of 150 lb.
- 4 built-in RJ45 jacks connect installed modem, router and other equipment to network
- Ships fully assembled for immediate installation

Package Includes

- SRWF3UDG SmartRack 3U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Structured Wiring Enclosure
- (2) Pre-installed 1U shelves
- Adjustable equipment brackets
- Combination lock instructions



16.5 in. deep, including network switches and patch panels

- Maximum load capacity of 150 lb.

Also Designed for Equipment Not Typically Mounted in Racks

- Pre-installed 1U shelves with adjustable metal brackets that attach to cabinet's square mounting holes
- Brackets accommodate modems, routers, firewalls and other non-rack devices
- Included thumbscrews secure equipment in place
- 4 built-in RJ45 jacks connect installed equipment to network

Keeps Important Equipment Secure

- Reversible front door locks securely with built-in combination lock to help prevent damage, tampering or theft
- Vented cabinet keeps equipment cool
- Brush-strip cable plates on either side allow easy cable routing while preventing dust from entering

Easy Enclosure and Equipment Installation

- Ships fully assembled for quick installation
- Wall-mounting holes spaced 16 in. apart for standard wall stud placement
- Brackets are easily adjustable for flexibility in storing equipment

Meets Payment Card Industry Standards

- Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Specifications

OVERVIEW	
UPC Code	037332205216
PHYSICAL	
Rack Height	3U
Maximum Device Depth (in.)	16.5
Maximum Device Depth (cm)	41.91
Shipping Dimensions (hwd / in.)	10.50 x 23.00 x 38.10
Shipping Dimensions (hwd / cm)	26.67 x 58.42 x 96.77
Shipping Weight (lbs.)	37.30
Shipping Weight (kg)	16.92
Unit Dimensions (hwd / in.)	35.56 x 20.00 x 7.07
Unit Dimensions (hwd / cm)	90.32 x 50.80 x 17.96



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Weight (lbs.)	30.90
Unit Weight (kg)	14.02
Color	Black
Weight Capacity - Stationary (lbs.)	150
Weight Capacity - Stationary (kg)	68
Maximum Device Depth (mm)	419
CERTIFICATIONS	
Certifications	EIA-310-E; IP20 Protection Rating
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>