

19 in. Blanking Panel Kit, 4 Pieces

MODEL NUMBER: SRXUPANEL



Improves cooling efficiency, optimizes airflow and prevents recirculation of hot air by filling in 1U to 15U of unused rack space.

Description

The SRXUPANEL Blanking Panel Kit fills unused spaces in your standard 19-inch rack. Not only does this give your rack a sleek, clean look, but it also protects your valuable rack equipment by improving airflow and cooling efficiency. By closing off unused rack openings, these blanking panels prevent hot air from recirculating through open spaces. This reduces operating costs, improves performance and provides longer lifespans for your equipment.

Constructed from heavy-duty cold-rolled steel in a durable black powder-coat finish to match most rack enclosures, the SRXUPANEL includes four blanking panels in different sizes: 1U, 2U, 4U and 8U. This gives you the flexibility to close off up to 15U in rack space in different configurations as needed. Just attach the desired panels to the rack's front vertical mounting rails using the included hardware.

Features

Improves Cooling Efficiency and Optimizes Airflow

- Closes off unused rack spaces to prevent hot air from recirculating around valuable equipment
- Reduces operating costs, improves performance, and provides longer lifespans for equipment
- Compatible with all standard 19 in. EIA-compliant racks

Premium Construction

- Made from heavy-duty cold-rolled steel in black powder-coat finish
- Includes 4 panels in 4 sizes: 1U, 2U, 4U and 8U
- Fills up to 15U of rack space
- Mounts easily using included hardware

Highlights

- Optimizes cooling of valuable rack equipment
- Prevents hot air from recirculating through open spaces
- Contains 4 panels in 4 sizes: 1U, 2U, 4U and 8U
- Made from heavy-duty cold-rolled black steel
- Includes mounting hardware

Package Includes

- 1U blanking panel
- 2U blanking panel
- 4U blanking panel
- 8U blanking panel
- (16) M6 screws
- (16) M6 cup washers
- (16) M6 cage nuts
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332188427
Accessory Type	Pass-Through Panel



Powering Business Worldwide



Accessory Class	Cooling Accessories
COOLING	
Cooling Type	Passive
PHYSICAL	
Shipping Dimensions (hwd / in.)	18.90 x 14.17 x 1.38
Shipping Dimensions (hwd / cm)	48.01 x 35.99 x 3.51
Shipping Weight (lbs.)	8.25
Shipping Weight (kg)	3.74
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.