

19 in. Blanking Panel Kit, 4 Pieces

MODEL NUMBER: **SRXUPANEL**



Improves cooling efficiency, optimizes airflow and prevents recirculation of hot air by filling in 1U to 15U of unused rack space.

Description

The SRXUPANEL Blanking Panel Kit fills unused spaces in your standard 19-inch rack. Not only does this give your rack a sleek, clean look, but it also protects your valuable rack equipment by improving airflow and cooling efficiency. By closing off unused rack openings, these blanking panels prevent hot air from recirculating through open spaces. This reduces operating costs, improves performance and provides longer lifespans for your equipment.

Constructed from heavy-duty cold-rolled steel in a durable black powder-coat finish to match most rack enclosures, the SRXUPANEL includes four blanking panels in different sizes: 1U, 2U, 4U and 8U. This gives you the flexibility to close off up to 15U in rack space in different configurations as needed. Just attach the desired panels to the rack's front vertical mounting rails using the included hardware.

Features

Improves Cooling Efficiency and Optimizes Airflow

- Closes off unused rack spaces to prevent hot air from recirculating around valuable equipment
- Reduces operating costs, improves performance, and provides longer lifespans for equipment
- Compatible with all standard 19 in. EIA-compliant racks

Premium Construction

- Made from heavy-duty cold-rolled steel in black powder-coat finish
- Includes 4 panels in 4 sizes: 1U, 2U, 4U and 8U
- Fills up to 15U of rack space
- Mounts easily using included hardware

Highlights

- Optimizes cooling of valuable rack equipment
- Prevents hot air from recirculating through open spaces
- Contains 4 panels in 4 sizes: 1U, 2U, 4U and 8U
- Made from heavy-duty cold-rolled black steel
- Includes mounting hardware

Package Includes

- 1U blanking panel
- 2U blanking panel
- 4U blanking panel
- 8U blanking panel
- (16) M6 screws
- (16) M6 cup washers
- (16) M6 cage nuts
- Installation guide



Specifications

OVERVIEW	
UPC Code	037332188427
COOLING	
Cooling Type	Passive
PHYSICAL	
Shipping Dimensions (hwd / cm)	48.01 x 35.99 x 3.51
Shipping Dimensions (hwd / in.)	18.90 x 14.17 x 1.38
Shipping Weight (kg)	3.74
Shipping Weight (lbs.)	8.25
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>