

## 20-30kVA 3-Phase Power Distribution Center with Integrated 3 breaker 208V Service Bypass Switch

MODEL NUMBER: **SUDC208V42P30M**



### Description

Tripp Lite's SUDC208V42P30M Power Distribution Cabinet supports 20-30kVA 3 phase UPS power distribution in critical datacenter equipment racks. Integrated 3 breaker 208v service bypass switch enables hot-swappable replacement of 20-30kVA 3 phase UPS systems without dropping the connected critical loads. Full size 42U rack enclosure with pre-installed 42 pole circuit breaker panel supports 3 phase 208V and single phase 208V and 120V outputs via optional corded receptacle whips, snap in panel breakers and PDUs. Breaker panel includes 225A, 3 pole main breaker, ground and neutral bars, plus 1/2, 3/4 and 1 inch knockouts. Rack enclosure offers secure front and rear doors, removable side panels and shares common dimensions and overhead wiring tray accessories as Tripp Lite SR42UB rack enclosures. Compatible with Tripp Lite SUBB-series 1, 2 and 3 pole breakers, SUWL-series corded receptacle whips and a full line of compatible basic, metered, monitored and switched PDUs to support a variety of advanced network configurations.

### Features

- SUDC208V42P30M Power Distribution Center supports 20-30kVA 3 Phase UPS power distribution in critical datacenter equipment racks
- Integrated 3 breaker 208v service bypass switch enables hot-swappable replacement of 20-30kVA 3 phase UPS systems without dropping the connected critical loads
- Full size 42U rack enclosure with pre-installed 42 pole circuit panel supports 3 phase 208V and single phase 208V and 120V outputs via optional corded receptacle whips, snap in panel breakers and PDUs
- Line up and match power distribution cabinet blends with existing standard datacenter racks for an aesthetically pleasing appearance while providing convenient connectivity between the centralized 3 phase UPS and protected electronic devices in equipment racks
- Breaker panel includes 225A 3 pole main breaker, ground and neutral bars, 1/2, 3/4 and 1 inch knockouts (see Help & Downloads for manual with detailed wiring information)
- Rack enclosure offers secure front and rear doors, removable side panels and shares common dimensions and overhead wiring tray and ladder accessories as Tripp Lite SR42UB equipment racks

### Highlights

- Full size 42U Rack Power Distribution Center supports 20-30kVA 3 phase UPS power distribution in datacenter equipment racks
- Integrated 3 breaker 208V service bypass switch enables hot-swap replacement of 20-30kVA 3 phase UPS systems without dropping the connected critical loads
- 42 pole breaker panel supports 3 phase, 208V and single phase 208V and 120V outputs to connected equipment
- Pre-installed 225A, 3 pole main breaker, ground and neutral bars
- Secure front and rear doors, removable side panels
- Full line of accessories includes circuit breakers, corded receptacle whips and PDUs



- Requires appropriate SUBB-series output circuit breakers (see Related Items for list of compatible SUBB breakers)
- Optional SUWL-series cable whips and SUWEL-series extensions support a variety of connector types, voltages and cable lengths (see Related Items for list of compatible SUWL-series and SUWEL-series cabling accessories)
- Optional full line of Basic, Metered, Monitored and Switched PDUs

## Specifications

OVERVIEW	
UPC Code	037332161581
INPUT	
PDU Input Voltage	208
PDU Plug Type	Hardwire
Input Phase	3-Phase
OUTPUT	
Output Receptacles	Hardwire
PHYSICAL	
Shipping Dimensions (hwd / cm)	214.63 x 66.04 x 114.30
Shipping Dimensions (hwd / in.)	84.50 x 26.00 x 45.00
Shipping Weight (kg)	235.41
Shipping Weight (lbs.)	519.00
Unit Dimensions (hwd / cm)	199.39 x 60.02 x 109.22
Unit Dimensions (hwd / in.)	78.5 x 23.63 x 43
Unit Weight (kg)	224.98
Unit Weight (lbs.)	496
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>