



Powering Business Worldwide

# Corded UPS Backplate Outlet Kit for SU6000RT3UHV UPS, 200/208/240V Input/Output, NEMA L6-30R

MODEL NUMBER: SUPDM11



### Highlights

- Converts Tripp Lite's hardware SU6000RT3UHV UPS system from hardware in/out to one with an AC plug and outlets
- 10 ft. / 3m AC input cord with NEMA L6-30P plug
- 2 NEMA L6-30R output receptacle
- Easy quick-connect wiring installs in minutes

### Description

Tripp Lite's SUPDM11 corded backplate kit converts Tripp Lite's hardware SU6000RT3UHV UPS system to one with an AC plug and outlet. 10 ft./3m input line cord with L6-30P plug enables connection to 200/208/240V 30A mains power. Two L6-30R output receptacles allow for the connection of high current equipment load or power distribution units (PDU). Easy quick-connect wiring installs in minutes.

### Features

- Converts Tripp Lite's hardware SU6000RT3UHV UPS system to one with an AC plug and outlet
- 10 ft./3m AC line cord with L6-30P input plug-in connection
- Two L6-30R output receptacles pass 200/208/240V output voltage on to connected equipment
- Easy quick-connect wiring installs in minutes

## Specifications

OVERVIEW	
UPC Code	037332120854
Accessory Type	Backplate Outlet Kit
Accessory Class	UPS Accessories
INPUT	
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	30A 200/208/240V
Input Connection Type	NEMA L6-30P



Powering Business Worldwide

OUTPUT	
Output Receptacles	(1) L6-30R
Output Nominal Voltage	200/208/240V
PHYSICAL	
Material of Construction	Steel
Shipping Dimensions (hwd / in.)	5.50 x 9.00 x 14.25
Shipping Dimensions (hwd / cm)	13.97 x 22.86 x 36.20
Shipping Weight (lbs.)	4.62
Shipping Weight (kg)	2.10
Unit Dimensions (hwd / in.)	3.000 x 3.750 x 4.750
Unit Dimensions (hwd / cm)	7.6 x 9.5 x 12.1
Unit Weight (lbs.)	4
Unit Weight (kg)	1.81
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.