

Internal Battery Pack - Compatible with select SmartOnline 20kVA, 30kVA, 40kVA 3-Phase UPS System & SUBF2030 External Battery Frame

MODEL NUMBER: **SURBC2030**



Description

The SURBC2030 Internal Battery Pack is a set of two pre-wired strings of internal batteries that are designed to be installed within the internal battery compartment for select Tripp Lite SmartOnline 20, 30 and 40kVA 3-Phase UPS System or SUBF2030 External Battery Frame. When installed as directed, the two assembled battery strings that make up a SURBC2030 maintain a nominal battery voltage of 240V DC. The SURBC2030 also serves as a replacement for existing internal battery packs.

Features

- Set of two pre-wired strings of internal batteries that are designed to be installed within the internal battery compartment of select Tripp Lite SmartOnline 20, 30 and 40kVA 3-Phase UPS System or SUBF2030 External Battery Frame
- When installed as directed, the two assembled battery strings that make up a SURBC2030 maintain a nominal battery voltage of 240V DC
- Also serves as a replacement for existing internal battery packs

Specifications

OVERVIEW	
UPC Code	037332141743
INPUT	
Input Phase	3-Phase

Highlights

- Internal Battery Pack offers extended runtime operation for select Tripp Lite SmartOnline 20, 30 and 40kVA 3-Phase UPS Systems & SUBF2030 External Battery Frame
- Simple installation scheme with pre-wired and assembled batteries

Package Includes

- SURBC2030 Internal Battery Pack (set of two pre-wired battery strings)
- Instruction and installation manual



BATTERY	
DC System Voltage (VDC)	240
UPS Connection	Included cabling
PHYSICAL	
External Battery Pack Form Factor	Tower
Shipping Dimensions (hwd / cm)	45.72 x 50.80 x 78.74
Shipping Dimensions (hwd / in.)	18.00 x 20.00 x 31.00
Shipping Weight (kg)	76.20
Shipping Weight (lbs.)	168.00
Unit Dimensions (hwd / cm)	- 20,3 x 15,2 x 68,6
Unit Dimensions (hwd / in.)	Each of the two battery strings measures - 8 x 6 x 27
Unit Weight (kg)	55.79
Unit Weight (lbs.)	123.00
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>