

## 208V 3-Phase Whip in 20 ft. (6.09 m) length with L21-30R output for 3-Phase Distribution Cabinet Applications

MODEL NUMBER: **SUWL2130C-20**



### Highlights

- 208V three phase whip distribution cabinet accessory
- 20-ft. (6.09 m) length with 3-ft. (0.91 m) removed outer jacket
- 5 conductor 10AWG stranded wire
- L21-30R outlet (208V 3PH 30A)

### Description

208V three phase whip with L21-30R outlet distributes power from 3 phase distribution cabinet to critical equipment racks. 20-ft. (6.09 m) insulated and 3-ft. (0.91 m) of removed outer jacket cabling supports hardwire connection to SUBB330 circuit breaker in SUDC208V series 3 phase distribution racks. L21-30R outlet is compatible with 208V loads and Power Distribution Units (PDUs) supporting a L21-30P plug-in connection.

### Features

- 208V three phase whip with L21-30R outlet
- Distributes power from 3 phase distribution cabinet to critical equipment racks
- 20-ft. (6.09 m) insulated and 3-ft. (0.91 m) of removed outer jacket cabling supports hardwire connection to SUBB330 circuit breaker in SUDC208V series 3 phase distribution racks
- L21-30R outlet is compatible with 208V loads and Power Distribution Units (PDUs) supporting a L21-30P plug-in connection

## Specifications

OVERVIEW	
UPC Code	037332176301
INPUT	
Input Connection Type	Hardwire (5 wire - L1, L2, L3, N, G)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>OUTPUT</b>	
PDU Recommendation Notes	Compatible with all PDU brands fitted with a L21-30P (208V 3PH 30A) input plug, including Tripp Lite &nbsp;<a class="productLink" href="//www.tripplite.com/8.6kW-3-Phase-Metered-PDU-208-120V-Outlets-36-C13-6-C19-6-5-15-20R-L21-30P-6ft-Cord-0U-Vertical-TAA-PDU3MV6L2130">PDU3MV6L2130</a>&nbsp;; PDU3VSR10L2130 and PDU3VSR3L2130
Output Receptacles	(1) L21-30R
<b>PHYSICAL</b>	
Color	Black
Cable Length (ft.)	20
Cable Length (m)	6.1
Shipping Dimensions (hwd / cm)	30.48 x 30.48 x 15.24
Shipping Dimensions (hwd / in.)	12.00 x 12.00 x 6.00
Shipping Weight (kg)	3.95
Shipping Weight (lbs.)	8.70
Unit Weight (kg)	5.22
Unit Weight (lbs.)	11.5
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>